353379-2 ✔ ACTIVE


AMP

TE Internal #: 353379-2

Other Automotive Connector Accessories, Other, Wire-to-Wire, Black, Operating Temperature Range -40 – 105 °C [-40 – 221 °F]

View on TE.com >

Connectors > Automotive Connectors > Connector Accessories > Other Connector Accessories



Automotive Connector Accessory Type: **Other**

Connector System: **Wire-to-Wire**

Primary Product Color: **Black**

Operating Temperature Range: **-40 – 105 °C [-40 – 221 °F]**

Features

Product Type Features

Automotive Connector Accessory Type	Other
Connector System	Wire-to-Wire

Body Features

Primary Product Color	Black

Usage Conditions

Operating Temperature Range	-40 – 105 °C[-40 – 221 °F]

Packaging Features

Packaging Quantity	1000
Packaging Method	Bag

Other

Serviceable	Yes

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211)

	Candidate List Declared Against: JAN 2021 (211) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability


Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: https://echa.europa.eu/guidance-documents/guidance-on-reach

Compatible Parts



TE Part # 353378-7
SQUIB CONN HSG YELLOW




TE Part # 1-353380-7
SQUIB CONN RETAINER ASSY 2P


Customers Also Bought



TE Part #6-176146-6
ECONOSEAL, CONNECTOR HOUSING




TE Part #1565963-2
MULTILOCK, RECEPTACLE AND TAB



TE Part #1473139-1
SQUIB 11DIA MK-2 PLUG HSG




TE Part #1473140-1
SQUIB 11DIA MK-2 LOCKING BUTTO



TE Part #1612120-1

11DIA SQUIB SLIM MK-2 PLUG HSG



TE Part #1612119-1

11DIA SQUIB SLIM MK-2 LOCKING



TE Part #1612123-1

SQUIB FERRITE



TE Part #1612122-1

SQUIB LOCKING BUTTON



TE Part #1612124-3

1DIA SOCKET AU



TE Part #1670108-1

BLIND PLUG FEMALE 1.5

Documents

Product Drawings

SQUIB CONN FERRITE

Japanese

CAD Files

Customer View Model

ENG_CVM_353379-2_A1.3d_igs.zip

English

Customer View Model

ENG_CVM_353379-2_A1.3d_stp.zip

English

Customer View Model

ENG_CVM_353379-2_A1.2d_dxf.zip

English

3D PDF

English

By downloading the CAD file I accept and agree to the Terms and Conditions of use.

Product Specifications

Application Specification

English

Socket Contact for Dia 1mm Pin (SQUIB Connector)

English

Instruction Sheets

Instruction Sheet (non U.S.)

English

Squib Connector

English

11dia squib connector checker

Japanese

Instruction Sheet (non U.S.)

Japanese

Instruction Sheet (non U.S.)

Japanese

Instruction Sheet (non U.S.)

Japanese