




Connectors > Rectangular Connectors > Rectangular Connector Accessories > Rectangular Boots & Strain Relief



Protection & Strain Relief Accessory Type: **Strain Relief**

Primary Product Material: **Nylon**

Primary Product Color: **Natural**

Operating Temperature Range: **-20 – 105 °C [-4 – 221 °F]**

Features

Product Type Features

Insert Supplied	Yes
Protection & Strain Relief Accessory Type	Strain Relief
Product Type	Accessory

Body Features

Primary Product Material	Nylon
Primary Product Color	Natural

Usage Conditions

Operating Temperature Range	-20 – 105 °C[-4 – 221 °F]
-----------------------------	---------------------------

Packaging Features

Packaging Method	Package
Packaging Quantity	1

Other

Comment	Strain relief part number represents one half of a strain relief. Two of a part number are required per connector., Strain relief
---------	---



part number represents one half of a strain relief. Two strain relief's are required per housing.

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JAN 2021 (211) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>





Compatible Parts


 TE Part # 350830-4 15P UMNL HDR ASSY PC 94VO LF	 TE Part # 350431-4 06P UMNL PINHDR ASSY V2 NAT LF	 TE Part # 350738-4 15P UMNL PIN HDR ASSY 94VO LF	 TE Part # 350732-4 06P UMNL PIN HDR ASSY 94VO LF
--	---	---	---




 TE Part # 350737-4 12P UMNL PIN HDR ASSY 94VO LF	 TE Part # 643429-1 15P UMNL HDR ASSY POL	 TE Part # 350828-4 09P UMNL HDR ASSY PC 94VO LF	 TE Part # 350732-1 06P UMNL PIN HDR ASSY 94VO
 TE Part # 350433-4 12P UMNL PIN HDR ASSY NATL LF	 TE Part # 350737-1 12P UMNL PIN HDR ASSY 94VO	 TE Part # 350587-1 12P UMNL PIN HDR ASSY V2 NATL	 TE Part # 350835-1 09P UMNL HDR ASSY PC 94VO
 TE Part # 350762-5 06P UMNL HDR ASSY PC LF	 TE Part # 350990-4 09P UMNL HDR ASSY LNG/TL	 TE Part # 350585-1 06P UMNL PIN HDR ASSY V2 NATL	 TE Part # 350783-1 12P UMNL CAP HSG
 TE Part # 350586-4 09P UMNL HDR ASSY PC NATL LF	 TE Part # 350711-1 06P UMNL PIN HDR ASSY 94VO	 TE Part # 350735-1 12P UMNL PLUG HSG	 TE Part # 350712-4 09P UMNL PIN HDR ASSY 94VO LF

Also in the Series | Universal MATE-N-LOK

 Circular Power Connectors(2)	 Connector Contacts(11)	 Insertion & Extraction Tools(4)	 Power Contacts(207)
---	--	--	--



Rectangular Boots & Strain Relief(35)



Rectangular Connector Adapters(7)



Rectangular Connector Housings(2)



Rectangular Connector Keying Plugs(3)



Rectangular Connector Locking(4)




Rectangular Connector Seals(26)



Rectangular Power Connectors(725)

Customers Also Bought



TE Part #1609989-6
CORCOM BCF SERIES 3-PHASE
FILTERS



TE Part #T4111012041-000
M12 M, 4P GOLD A_CODE S
SHIELDED PG9



TE Part #1-770252-0
UMNL II PIN LP 14-18



TE Part #1623257-1
CRG0805 1% 5K1




TE Part #2-747579-7
SHLDING FERRULE,PLTD TIN,BULK



TE Part #1-350589-0
STR/REL CLAMP NATL



TE Part #1-640415-1
UMNL KEYING PLUG V2 NATL



TE Part #2822623004
44A0111-12-0



TE Part #1-925017-5
250 FASTON HSG.,REC.,1 POS,BLACK



TE Part #169475-1
MINI CERTI-LOK III+

Documents



Product Drawings

STR/REL CLAMP UMNL

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_350812-1_P.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_350812-1_P.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_350812-1_P.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

SOFT_SHELL_PIN_SOCKET_CONNECTORS_STANDARD_DENSITY

English

Instruction Sheets

Instruction Sheet (U.S.)

English