329331 ✔ ACTIVE

TE Internal #: 329331

RF Connector Ferrules, RG 196A Compatible With RF Cable Type, Brass, Zinc Ferrule Plating Material

View on TE.com >

Connectors > RF Coax Connectors > RF Coax Accessories > Ferrules







Compatible With RF Cable Type: **RG 196A**

Ferrule Material: **Brass**

Ferrule Plating Material: **Zinc**

Features

Product Type Features

Connector Type	Shielded Wire Crimp
Compatible With RF Cable Type	RG 196A

Body Features

Color Code	Violet
Body Plating Material	Tin

Contact Features

Ferrule Material	Brass
Ferrule Plating Material	Zinc

Dimensions

Accepts Wire Insulation Diameter Range	.84 – 1.5 mm[.033 – .059 in]

Packaging Features

Packaging Method	Bag

Product Compliance

For compliance documentation, visit the product page on TE.com>


EU RoHS Directive 2011/65/EU	Compliant

EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JAN 2021 (211) Does not contain REACH SVHC
Halogen Content	Not Yet Reviewed for halogen content
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: https://echa.europa.eu/guidance-documents/guidance-on-reach

Compatible Parts




TE Part # 59500
SAHT TERMASHIELD FERR ASSY


Customers Also Bought




TE Part #1-6609130-4
CORCOM M SERIES MULTI-FUNCTION INLET FIL



TE Part #1-5066683-0
D-Sub Conn Contacts: Socket, Phosphor Bronze, Signal, Size 20



TE Part #5111595-6
026 ASSY SYS 50 PADDLEBOARD



TE Part #1-796634-1
11 POS 5.08MM R/A PLUG,TRM BLK




TE Part #33717
TERMINAL,BUDG R 16-14HD 8




TE Part #3-1676913-8
YR1 0.1% 226K



TE Part #6-1676913-1
YR1 0.1% 280R



TE Part #CL9153-000
Low Profile Heat Shrink Boots: Poly Mold, Lipped, Right Angle



TE Part #1617073-4
3SBC1778A2 = M39016/13-112L



TE Part #1-459585-0
CRIMPER AMPLIVAR SPLICE BLUNTF

Documents

Product Drawings

T-SHIELD,.033-.059

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_329331_V.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_329331_V.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_329331_V.3d_stp.zip

English

By downloading the CAD file I accept and agree to the Terms and Conditions of use.

Datasheets & Catalog Pages

1307191 RF Coax Products Catalog

English