



Connectors > Rectangular Connectors > Rectangular Connector Accessories > Rectangular Caps & Covers



Protection & Strain Relief Accessory Type: **Strain Relief Coverpart Kit**

Compatible With Connector Style: **Receptacle**

Sealable: **No**

Circuit Application: **Power**

Connector Mounting Type: **Cable Mount (Free-Hanging)**

Features

Product Type Features

Product Type	Accessory
Protection & Strain Relief Accessory Type	Strain Relief Coverpart Kit
Sealable	No

Body Features

Color	Black
Material	Nylon

Mechanical Attachment

Connector Mounting Type	Cable Mount (Free-Hanging)
-------------------------	----------------------------

Usage Conditions

Compatible With Connector Style	Receptacle
Operating Temperature Range	-20 – 85 °C[-4 – 185 °F]

Operation/Application

For Use With	Receptacle housing
Circuit Application	Power

Industry Standards

VDE Tested	No
UL Flammability Rating	UL 94V-0

Packaging Features

Packaging Method	Box & Carton
------------------	--------------



Packaging Quantity	500
Other	
Comment	Kit includes MNL Hsg 794616-4, cover halves 293728-1 and 293729-1

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JAN 2021 (211) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts






Customers Also Bought




TE Part #1-86557-9
2.54mm FFC Connectors Pin Contacts



TE Part #2106091-3
4 pos Inverted Thru Board SMT Header




TE Part #1-794608-0
PIN CONT 20-24 TIN PLATE STRIP



TE Part #2106091-1
2 pos Inverted Thru Board SMT Header



TE Part #2-794615-4
PANEL MT DBL ROW HSG 24 POS



TE Part #103682-5
06 MTE PANEL MOUNT SR



TE Part #1-2329360-2
PB OFF/ON RC RED M3 TERM. IP68



TE Part #2-794615-2
PANEL MT DBL ROW HSG 22 POS



TE Part #2029047-4
4P MICRO MNL RCPT HSG SR SIDE



TE Part #YAFD57-14-18PYC012
PLUG ASSY

Documents

Product Drawings
4 pos. coverpart (kit) for P/N 794616-4
English

Product Specifications
Application Specification
English