T3609200112-000 ✔ ACTIVE

HDC



TE Internal #: T3609200112-000

Rectangular Backshells & Clamps, Cable Gland, Sealable

View on TE.com >

Connectors > Rectangular Connectors > Rectangular Connector Accessories > Rectangular Backshells & Clamps



Backshell & Clamp Accessory Type: **Cable Gland**

Sealable: **Yes**

Features

Product Type Features

Backshell & Clamp Accessory Type	Cable Gland
Sealable	Yes

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant with Exemptions
EU ELV Directive 2000/53/EC	Compliant with Exemptions
China RoHS 2 Directive MIIT Order No 32, 2016	Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JAN 2021 (211) SVHC > Threshold: Pb (1.9% in Component Part) **Article Safe Usage Statements:** Do not eat, drink or smoke when using this product. Wash thoroughly after handling. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location.
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not reviewed for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: https://echa.europa.eu/guidance-documents/guidance-on-reach

Compatible Parts



TE Part # T3165200111-000
BLIND-20-M




TE Part # T1190102032-000
H10B-TGH/TSH-M32/2M20



TE Part # T1220100120-000
H10B-TG-M20



TE Part # T1360062120-000
H6B-TGB-M20



TE Part # T3161200050-000
LN-20-M

Customers Also Bought



TE Part #1393030-8
P&B SSR SERIES SOLID STATE RELAYS



TE Part #1469920-2
Mini Pak HD Micro TCA Power Conn



TE Part #1057159-1
3004 7941 00



TE Part #YDTS26W23-21BCV001
D38999: Straight Plug, 23-21 Insert




TE Part #102095-3
MOD IV PIN PLTD 30 SEL



TE Part #104069-4
10 SYSTEM 50 HDR DRRA SHRD



TE Part #1051852-1
2032 5002 00



TE Part #103165-6
20 MODII HDR DRRA 3/4SHRD .100



TE Part #1045422-1
SSMA R/A Cable Plug 1007 7985 00



TE Part #1338742-1
SEAT TL.6 ROW,HS3 D BM.60 POS

Documents

Product Drawings

DLX-20-MT

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_T3609200112-000_A.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_T3609200112-000_A.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_T3609200112-000_A.3d_stp.zip

English

By downloading the CAD file I accept and agree to the Terms and Conditions of use.

Datasheets & Catalog Pages

Heavy Duty Connectors

English

HEAVY DUTY CONNECTORS

English

Product Specifications

Application Specification

English

Product Environmental Compliance

Product Compliance

English

Product Compliance

English