



Wire Protection & Management > Heat Shrink Molded Shapes > Bushings & Bobbins



Heat Shrink Component Product Type: **Bushing**
 Heat Shrink Component Accessory Color: **Black**
 Heat Shrink Component Accessory Width: **15.2 mm [.6 in]**
 Molded Part Type: **Accessories**
 Heat Shrink Component Accessory Material: **Modified Elastomer**

Features

Product Type Features

Heat Shrink Component Product Type	Bushing
Molded Part Type	Accessories

Body Features

Heat Shrink Component Accessory Color	Black
Heat Shrink Component Accessory Material	Modified Elastomer
Pliancy	Flexible

Dimensions

Length	101.6 mm[4 in]
Heat Shrink Component Accessory Width	15.2 mm[.6 in]

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JAN 2021 (211) SVHC > Threshold:



Octamethylcyclotetrasiloxane (D4) (.24%)

Article Safe Usage Statements:

Wash thoroughly after handling. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location.

Halogen Content

Not Yet Reviewed for halogen content

Solder Process Capability

Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # CJ2087-000
[HL2010E-KIT-120V](#)

Also in the Series | Raychem SEB



[Bushings & Bobbins\(5\)](#)




[Cable Transitions & Breakouts\(1\)](#)

Customers Also Bought



TE Part #0660-206-0882
CONT PIN



TE Part #2-1617072-4
3SBC1506A2 = M39016/13-060L



TE Part #33463
TERMINAL,SOLIS R 8 3/8




TE Part #242489-000
CWT-3811



TE Part #4-1969541-0
RETAINER, TPA, DUAL ROW, EP2.5




TE Part #1532179-7
M83513/03-A11N, MCKS-N1-B-9P6Q9-18.0



TE Part #218052-005
55A0811-14-9



TE Part #316078-000
55A1131-20-3/6/9-9



TE Part #YDTS33W25RV0010000
DUST COVER ASSEM



TE Part #2-1618399-5
MS18-1006=Relay Solid State

Documents

Product Drawings

SEB-D

English

Datasheets & Catalog Pages

1654025_Sec4_SEB

English

Harness Repair Products Quick Reference Guide

English