



Connectors > Circular Connectors > Standard Circular Connectors



Connector System: **Wire-to-Wire**
Connector & Contact Terminates To: **Wire & Cable**
Reverse Gender: **No**
Circular Connector Insulation Material Type: **PBT**
Hermetically Sealed: **No**

Features

Product Type Features

Connector System	Wire-to-Wire
Connector & Contact Terminates To	Wire & Cable

Configuration Features

Contacts Preloaded	No
--------------------	----

Body Features

Circular Connector Insulation Material Type	PBT
Hermetically Sealed	No

Contact Features

Reverse Gender	No
----------------	----

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JUN 2020 (209) SVHC > Threshold:



Not Yet Reviewed

Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not reviewed for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 2213351-2
NECTOR M SEAL/CABLE CLAMP
ASSEMBLY, 17MM

Also in the Series | NECTOR M Series



Circular Connector Hardware(1)




Plug & Socket Lighting Connector
Accessories(1)



Rectangular Connector Hardware(13)



Rectangular Power Connectors(3)



Customers Also Bought

TE Part #2120338-3
SCREEN CLAMP

TE Part #2120339-1
SIDE CLIP

TE Part #1103428-1
MALE INSERT CRIMP, 8-POS. TYPE III+

TE Part #2120432-3
CRIMP SLEEVE

TE Part #TAD14741311-002
Ethernet, Sercos-III M12-D 4p PVC Red DE

TE Part #2213223-1
NECTOR M PANEL MOUNT SEAL

TE Part #2213225-1
NECTOR M SKT HSG ASSY, PM, 5P CODE A

TE Part #1103426-1
MALE INSERT, CRIMP, 4-POS. 22DF CONTACTS

TE Part #1-2213266-2
NECTOR M PIN, CRIMP, 16-18 AWG

TE Part #1-2213265-2
NECTOR M SKT, CRIMP, 16-18 AWG

Documents

Product Drawings
NECTOR M SEAL/CABLE CLAMP ASSEMBLY, 14MM
English

CAD Files
3D PDF
3D
Customer View Model
ENG_CVM_CVM_2213351-1_A.2d_dxf.zip



English

Customer View Model

[ENG_CVM_CVM_2213351-1_A.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_2213351-1_A.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

[5-1773465-6_NECTOR_M](#)

English