



Connectors > Circular Connectors > Circular Connector Accessories > Circular Connector Hardware



Circular Connector Hardware Type: **Nut**

Corrosion Protected: **Yes**

Features

Product Type Features

Circular Connector Hardware Type	Nut
----------------------------------	-----

Usage Conditions

Corrosion Protected	Yes
---------------------	-----

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JUN 2020 (209) SVHC > Threshold: Not Yet Reviewed
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not reviewed for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits



as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>


Compatible Parts



TE Part # 2213229-2


NECTOR M RING NUT, 5/6/7P, 14-17MM

Customers Also Bought



TE Part #1-2176315-7

MELF SMA_A 2K2 0.1% 15PPM 0204 0.4W



TE Part #2-2176315-0

MELF SMA_A 3K9 0.1% 15PPM 0204 0.4W



TE Part #Y12345-000

ALR-SC-10A



TE Part #2213223-1

NECTOR M PANEL MOUNT SEAL



TE Part #2213225-1

NECTOR M SKT HSG ASSY, PM, 5P CODE A



TE Part #2213228-1

NECTOR M HSG, PIN, FREE HANG, 5P CODE A

TE Part #2213226-3

NECTOR M POSITIONER HOUSING



TE Part #2213229-2

NECTOR M RING NUT, 5/6/7P, 14-17MM



TE Part #1-2213266-2

NECTOR M PIN, CRIMP, 16-18 AWG

TE Part #1-2213265-2

NECTOR M SKT, CRIMP, 16-18 AWG

Documents

Product Drawings

NECTOR M RING NUT, 5/6/7P, 11-14MM

English



CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_2213229-1_A.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_2213229-1_A.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_2213229-1_A.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

5-1773465-6_NECTOR_M

English