

TE Internal #: 2199249-4
PCB Spring Contact, C-Clip, Scalable, Side Protected,
Uncompressed Height 2.3 mm [.091 in], Length 3.2 mm [.126 in],
Width .059 in [1.5 mm]
[View on TE.com >](#)



Connectors > PCB Connectors > Board-to-Board Connectors > PCB Spring Contacts



Spring Finger Type: **C-Clip**
Scalable: **Yes**
Side Protected: **Yes**
Uncompressed Height: **2.3 mm [.091 in]**
Contact Length: **3.2 mm [.126 in]**

Features

Product Type Features

Spring Finger Type	C-Clip
Scalable	Yes
Connector System	Board-to-Board
Sealable	No
Connector & Contact Terminates To	Printed Circuit Board

Configuration Features

Side Protected	Yes
Number of Positions	1

Contact Features

Contact Underplating Material	Nickel
PCB Contact Termination Area Plating Material	Gold
Contact Base Material	Copper Alloy
Contact Length	3.2 mm[.126 in]
Contact Width	1.5 mm[.059 in]



Contact Working Range (Low)	1.4 mm[.055 in]
Contact Working Range (High)	2.1 mm[.083 in]
Point of Contact Area Plating Material	Gold
Contact Current Rating (Max)	2 A

Dimensions

Uncompressed Height	2.3 mm[.091 in]
---------------------	-----------------

Usage Conditions

Operating Temperature Range	-40 – 85 °C[-40 – 185 °F][-40 – 185 °F]
-----------------------------	---

Operation/Application

Circuit Application	Signal
---------------------	--------

Packaging Features

Packaging Quantity	6000
Packaging Method	Tape & Reel

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JAN 2021 (211) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Reflow solder capable to 260°C

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on



requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 2306454-3
SPRING FINGER 2.3H

Customers Also Bought



TE Part #1-1735446-2
AMP HPI 2.0MM HEADERS



TE Part #1-2141272-1
HIGH VOLTAGE HEADER



TE Part #1379029-1
MQS, CONNECTOR HOUSING



TE Part #964328-1
TIMER, RECEPTACLE AND TAB



TE Part #1-1740196-2
D-Sub Receptacle Assy: Eurostyle,
Right Angle, Surface Mount, 2.74mm



TE Part #1-1623782-9
Wirewound Resistor: Vertical Mount



TE Part #1-1879214-9
CPF 0402 499R 0.1% 25PPM 1K RL



TE Part #1-1775333-0
0.5mm FPC Connectors



TE Part #1320928-2
STRIP GUIDE



TE Part #1-1969543-0
ASSY, HDR, VERT, 10P, DUAL ROW,
EP2.5

Documents

Product Drawings
Shield Finger, Loose Piece, Type B, 2.3h
English



CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_2199249-4_A2.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_2199249-4_A2.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_2199249-4_A2.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

Product Specification

English

Product Environmental Compliance

TE Material Declaration

English