



Connectors > Rectangular Connectors > Rectangular Connector Accessories > Rectangular Connector Hardware



Hardware Type: **Screw Kit**
Connector System: **Wire-to-Panel**
Sealable: **No**
Connector & Contact Terminates To: **Wire & Cable**
Circuit Application: **Power & Signal**

Features

Product Type Features

Product Type	Accessory
Connector System	Wire-to-Panel
Sealable	No
Connector & Contact Terminates To	Wire & Cable

Body Features

Material	Stainless Steel
----------	-----------------

Mechanical Attachment

Screw & Hole Thread Size	M4 x 0.7-6G
Hardware Type	Screw Kit
Connector Mounting Type	Panel Mount

Dimensions

Length	31.09 mm[1.224 in]
--------	--------------------

Usage Conditions

Operating Temperature Range	-55 – 130 °C[-67 – 266 °F]
-----------------------------	----------------------------

Operation/Application

For Use With	Plug Housing
Circuit Application	Power & Signal

Packaging Features

--	--



Packaging Quantity	1
Packaging Method	Bag

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JAN 2021 (211) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability


Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 208210-2
METRIMATE SOCKET 19 POSN



TE Part # 208211-6
SCREW,SHOULDER,SPECIAL

Customers Also Bought



TE Part #1-640454-2
Polyester Vertical PCB Header: 2.54 mm, With Mating Alignment, Unshrouded

TE Part #1445828-3
MINI CPC

TE Part #1-2834238-1
SLIMSEAL MINIATURE HEADERS

TE Part #1-1658526-8
609-3430LF FEM SOCKET, LEAD FREE

TE Part #1766811-1
CONTACT, PIN, #0

TE Part #175658-1
MULTILOCK, CONNECTOR HOUSING

TE Part #CN9922-000
SBP SELF LAMINATING VINYL LABELS

TE Part #172106-2
V-TYPE E.I.S. CONN. 2P ASSY

TE Part #1-87523-8
MOD IV RECP PLTD 30 DPLX

Documents

Product Drawings

HARDWARE KIT,DRAWER CONN

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_213283-2_H.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_213283-2_H.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_213283-2_H.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages



METRIMATE_PIN_SOCKET_CATALOG

English

Product Specifications

Application Specification

English

Product Environmental Compliance

TE Material Declaration

English