



Wire Protection & Management > Interconnect Devices > SolderSleeve Shield Terminators



SolderSleeve Shield Terminator Product Type: **Shield Terminator**

SolderSleeve Shield Terminator Operating Temperature (Max): **125 °C**

SolderSleeve Shield Terminator Expanded Inside Diameter (Min): **33.02 mm [1.3 in]**

SolderSleeve Shield Terminator Recovered Inside Diameter (Max): **19.05 mm [.75 in]**

Pre-Installed Lead: **No**

Features

Product Type Features

Splice Type	SolderSleeve
SolderSleeve Shield Terminator Product Type	Shield Terminator

Configuration Features

Pre-Installed Lead	No
--------------------	----

Termination Features

Termination Method	Solder
--------------------	--------

Dimensions

Overall Length	33 mm[1.3 in]
SolderSleeve Shield Terminator Expanded Inside Diameter (Min)	33.02 mm[1.3 in]
SolderSleeve Shield Terminator Recovered Inside Diameter (Max)	19.05 mm[.75 in]

Usage Conditions

SolderSleeve Shield Terminator Operating Temperature (Max)	125 °C
Resistance Properties	Splash Protection
Wire Temperature (Max)	85 °C

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Not Compliant
------------------------------	---------------



EU ELV Directive 2000/53/EC	Not Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JAN 2021 (211) SVHC > Threshold: Cd (18% in Solder) Article Safe Usage Statements: Use personal protective equipment as required. Do not eat, drink or smoke when using this product. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location.
Halogen Content	Out of Scope - excluded from Halogen requirements
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # CJ2087-000
HL2010E-KIT-120V


Customers Also Bought



TE Part #300329-000
Heat Shrink Boots: Poly Mold, Lipped



TE Part #282301-002
44A0211-8-9




TE Part #152169-000
382A046-25/225-0



TE Part #YDTS26Z17-99PNV001
D38999: Straight Plug, 17-99 Insert





TE Part #2822623004
44A0111-12-0




TE Part #185652-000
ST18-3-55-22-90




TE Part #1864273001
99M0111-16-54



TE Part #1-1634200-7
PREDD3-07F-BB0FW



TE Part #2820063010
44A0111-16-6



TE Part #2820023007
44A0111-16-2

Documents

Product Drawings

B-051-02-01

English

Datasheets & Catalog Pages

Raychem Electrical Interconnect Products

English

Product Specifications

Product Specification

English