



Wire Protection & Management > Interconnect Devices > SolderSleeve Shield Terminators



SolderSleeve Shield Terminator Operating Temperature (Max): 150 °C

SolderSleeve Shield Terminator Expanded Inside Diameter (Min): 2.67 mm [.105 in]

SolderSleeve Shield Terminator Recovered Inside Diameter (Max): 1.4 mm [.055 in]

Pre-Installed Lead: No

Resistance Properties: Immersion Protection

Features

Configuration Features

Pre-Installed Lead	No
--------------------	----

Dimensions

SolderSleeve Shield Terminator Expanded Inside Diameter (Min)	2.67 mm[.105 in]
SolderSleeve Shield Terminator Recovered Inside Diameter (Max)	1.4 mm[.055 in]

Usage Conditions

SolderSleeve Shield Terminator Operating Temperature (Max)	150 °C
Resistance Properties	Immersion Protection
Wire Temperature (Max)	150 °C

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Not Compliant
EU ELV Directive 2000/53/EC	Not Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JAN 2021 (211) SVHC > Threshold: Pb (37% in Solder) Article Safe Usage Statements:



Do not eat, drink or smoke when using this product. Wash thoroughly after handling. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location.

Halogen Content	BFR/CFR/PVC Free, but Br/Cl >900 ppm in other sources.
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

TE Part # CJ2087-000
HL2010E-KIT-120V

Customers Also Bought

TE Part #0567590001
TMS-SCE MILITARY GRADE SLEEVES

TE Part #1757820-6
AMPLIMITE,ASY,RCPT,STD,109,ZN,1,CT

TE Part #1757819-6
AMPLIMITE,ASY,PLUG,STD,109,ZN,1,CT

TE Part #1-5111595-5
080 ASSY SYS 50 PADDLEBOARD

TE Part #1-102159-0
AMP-LATCH UNIVERSAL HEADERS

TE Part #118577-000
S01-05-R

TE Part #1379193001
VG-95218-T020-A001

TE Part #1-87195-8
MOD IV RECP LP



TE Part #0950443001
VG-95218-T020-E069



TE Part #NB08762001
ATUM-9/3-X-STK

Documents

Product Drawings

S01-02-R

English

Datasheets & Catalog Pages

1654025_Sec8_B-155_CWT_SO63_S01to03_SO96

English

Raychem Electrical Interconnect Products

English