1SNA206230R1100 ✔ ACTIVE

TE Internal #: 1SNA206230R1100

Terminal Block & Strip Marking Accessories, Marker Card, Green, Operating Temperature Range 55 – 110 °C [131 – 230 °F], UL 94V-2

View on TE.com >

Connectors > Terminal Blocks & Strips > Terminal Block & Strip Accessories > Terminal Block & Strip Marking Accessories

Marking Product Type: **Marker Card**

Primary Product Color: **Green**

Operating Temperature Range: **55 – 110 °C [131 – 230 °F]**

UL Flammability Rating: **UL 94V-2**

Features

Product Type Features

Marking Product Type	Marker Card

Body Features

Primary Product Color	Green

Usage Conditions

Operating Temperature Range	55 – 110 °C[131 – 230 °F]

Printer/Label Features

Label Material	Polyamide

Industry Standards

UL Flammability Rating	UL 94V-2

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JAN 2021 (211) Does not contain REACH SVHC

Halogen Content	Not Yet Reviewed for halogen content
Solder Process Capability	Not reviewed for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: https://echa.europa.eu/guidance-documents/guidance-on-reach


Compatible Parts



TE Part # 1SNK536010R0000
ZS240




TE Part # 1SNK900001R0000
BAM4



TE Part # 1SNA105055R2400
M6/8.SNB



TE Part # 1SNA105124R1600
M35/16



TE Part # 1SNA105129R2300
M16/12




TE Part # 1SNA105135R1100
M4/8.SF2



TE Part # 1SNA105265R0300
MS4/6




TE Part # 1SNA115124R0700
M35/16




TE Part # 1SNA115129R1400
M16/12



TE Part # 1SNA115265R2400
MS4/6




TE Part # 1SNA115604R2100
M4/8.D2.SF



TE Part # 1SNA115646R2200
M4/8.D2.SFL



TE Part # 1SNA115657R2500
M4/8.SF



TE Part # 1SNA115659R0700
M4/8.SN




TE Part # 1SNA115662R2200
M4/8.SFT




TE Part # 1SNA115665R2500
M4/8.SFDT



TE Part # 1SNA115667R2700
M4/8.SFLT



TE Part # 1SNA115668R0000
M4/8.SNT



TE Part # 1SNA115688R2500
M6/8.SNB



TE Part # 1SNA115935R0400
M4/8.SFD3

Customers Also Bought



TE Part #0462-209-16141
DEUTSCH SOLID CONTACTS



TE Part #W6P
DEUTSCH DT WEDGELOCKS



TE Part #114017-ZZ
DEUTSCH SEALING PLUGS



TE Part #1-480698-0
02P UMNL PLUG HSG NATL



TE Part #1SNA199412R1500
SCH8



TE Part #1SNA233000R0100
RC610

TE Part #1SNA234000R0200
RC810

Documents

CAD Files

3D PDF

3D

Customer View Model
ENG_CVM_CVM_1SNA206230R1100_A2.2d_dxf.zip

English

Customer View Model
ENG_CVM_CVM_1SNA206230R1100_A2.3d_stp.zip

English

By downloading the CAD file I accept and agree to the **Terms and Conditions** of use.

Datasheets & Catalog Pages

RC 610 VIERGE VERT

English

ENTRELEC Terminal Block - Master Catalog

English