



Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Not Yet Reviewed
Halogen Content	Not Yet Reviewed for halogen content
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulations, TE’s information on SVHC in articles for this part number is still based on the European Chemical Agency (ECHA) ‘Guidance on requirements for substances in articles’(Version: 2, April 2011), applying the 0.1% weight on weight concentration threshold at the finished product level. TE is aware of the European Court of Justice ruling of September 10th, 2015 also known as O5A (Once An Article Always An Article) stating that, in case of ‘complex object’, the threshold for a SVHC must be applied to both the product as a whole and simultaneously to each of the articles forming part of its composition. TE has evaluated this ruling based on the new ECHA “Guidance on requirements for substances in articles” (June 2017, version 4.0) and will be updating its statements accordingly.

Also in the Series | Industrial RJ45 Variant 14



Circular Ethernet Hardware(1)



Circular RJ45 Connectors(2)



RJ45 Connectors(4)

Customers Also Bought




TE Part #5-747905-2
9 Rcpt Solder Cup, Gold Flash,



TE Part #3-640426-4
04P MTA156 CONN ASSY 18AWG
ORA



TE Part #207489-1
FLEXIBLE CABLE BOOT, SIZE 11



TE Part #207490-1
CABLE GRIPPER, SIZE 11




TE Part #3-643816-6
Nylon Tin Plated Receptacle: 2.54mm,
With Mating Alignment, MTA 100



TE Part #462378-000
Low Profile Heat Shrink Boots: Poly
Mold, Lipped, Right Angle



TE Part #5580634002
Single Wall VPB: Heat Shrink Tubing, 2:
1 Shrink Ratio



TE Part #282928-000
44A0111-18-900



TE Part #395605-000
44A0141-20-MST4CS2275



TE Part #YDTS33T19NV0010000
CAP ASSEMBLY

Documents

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_1987672-1_A.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_1987672-1_A.3d_igs.zip



English

Customer View Model

[ENG_CVM_CVM_1987672-1_A.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

[1-1773733-5_RJ45_VARIANT14_FLYER](#)

English

Agency Approvals

[UL Report](#)

English