



Wire Protection & Management > Interconnect Devices > SolderSleeve Shield Terminators



SolderSleeve Shield Terminator Product Type: **Shield Terminator**

SolderSleeve Shield Terminator Operating Temperature (Max): **150 °C**

SolderSleeve Shield Terminator Expanded Inside Diameter (Min): **6.99 mm [.275 in]**

SolderSleeve Shield Terminator Recovered Inside Diameter (Max): **4.32 mm [.17 in]**

Pre-Installed Lead: **Yes**

Features

Product Type Features

Splice Type	Shield Terminator
Temperature Indicator Type	None
Temperature Indicator	None
SolderSleeve Shield Terminator Product Type	Shield Terminator

Configuration Features

Pre-Installed Lead Type	Yes
Pre-Installed Lead	Yes

Body Features

Lead Color	White/Black
Lead Plating Material	Tin
Lead Stranding	Stranded

Termination Features

Termination Method	Solder
--------------------	--------

Dimensions

Pre-Installed Lead Wire Size	.61 mm²
Shield Outside Diameter (Min)	4.3 mm[.17 in]
Overall Length	19.1 mm[.75 in]
Jacket Outside Diameter	7 mm[.275 in]



SolderSleeve Shield Terminator Expanded Inside Diameter (Min)	6.99 mm[.275 in]
SolderSleeve Shield Terminator Recovered Inside Diameter (Max)	4.32 mm[.17 in]

Usage Conditions

SolderSleeve Shield Terminator Operating Temperature (Max)	150 °C
Resistance Properties	Immersion Protection
Wire Temperature (Max)	150 °C

Industry Standards

Government Qualified	No
MIL/NAS Specification (MIL-S-83519, NAS-1747)	RT-1404

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Not Compliant
EU ELV Directive 2000/53/EC	Not Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JAN 2021 (211) SVHC > Threshold: Pb (37% in Solder) Article Safe Usage Statements: Do not eat, drink or smoke when using this product. Wash thoroughly after handling. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location.
Halogen Content	BFR/CFR/PVC Free, but Br/Cl >900 ppm in other sources.
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer


This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts




TE Part # CJ2087-000
HL2010E-KIT-120V

Customers Also Bought



TE Part #657691-000
Heat Shrink Boots: Poly Mold, Lipped




TE Part #3-1879617-4
H8 240R 1% 15PPM



TE Part #ABC03O-20P-4048
IN-LINE RECP



TE Part #3161413001
55A1121-24-9/9-9



TE Part #438449-000
82A0112-8-9



TE Part #ZPF000000000018696
FDBA 50-8-98 PN-K-A246



TE Part #5-2176366-1
RQ 0603 1K43 0.1% 10PPM 1K RL



TE Part #5059070049
TRSA-1014/C/1/A



TE Part #5059070025
TRSA-1014/C/1/S



TE Part #5059080050
TRSA-1014/C/2/20

Documents

Product Drawings

ST63-5-55-20-90

English

Datasheets & Catalog Pages

Raychem Electrical Interconnect Products

English

Product Specifications



Product Specification

English