



Wire Protection & Management > Interconnect Devices > SolderSleeve Shield Terminators



SolderSleeve Shield Terminator Product Type: **Shield Terminator**

SolderSleeve Shield Terminator Operating Temperature (Max): **125 °C**

SolderSleeve Shield Terminator Expanded Inside Diameter (Min): **6 mm [.236 in]**

SolderSleeve Shield Terminator Recovered Inside Diameter (Max): **3.3 mm [.13 in]**

Pre-Installed Lead: **Yes**

Features

Product Type Features

Temperature Indicator	Yes
Temperature Indicator Type	Thermochromic
SolderSleeve Shield Terminator Product Type	Shield Terminator

Configuration Features

Pre-Installed Lead Type	XL Polyethylene
Pre-Installed Lead	Yes

Body Features

Lead Color	White
Lead Plating Material	Tin
Lead Stranding	Stranded (W1)

Dimensions

Pre-Installed Lead Wire Size	.38 mm²
Overall Length	32 mm[1.26 in]
Shield Outside Diameter (Min)	3.3 mm[.13 in]
Jacket Outside Diameter	6 mm[.236 in]
SolderSleeve Shield Terminator Expanded Inside Diameter (Min)	6 mm[.236 in]
SolderSleeve Shield Terminator Recovered Inside Diameter (Max)	3.3 mm[.13 in]

Usage Conditions

--



SolderSleeve Shield Terminator Operating Temperature (Max)	125 °C
Resistance Properties	Splash Protection
Wire Temperature (Max)	85 °C

Industry Standards

Government Qualified	No
----------------------	----

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Not Compliant
EU ELV Directive 2000/53/EC	Not Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JAN 2021 (211) SVHC > Threshold: Pb (32% in Solder) Cd (18% in Solder) Article Safe Usage Statements: Use personal protective equipment as required. Do not eat, drink or smoke when using this product. Wash thoroughly after handling. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location.
Halogen Content	BFR/CFR/PVC Free, but Br/Cl >900 ppm in other sources.
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # CJ2087-000
[HL2010E-KIT-120V](#)


Customers Also Bought



TE Part #1-1375820-2
Receptacle Housing: 2.54mm, 1 Row, CST-100 II



TE Part #205560-2
AMPLIMITE,ASY,PLUG,STD,109,3



TE Part #204512-2
RECEPT ASSY,SZ 1,AMPLIMITE



TE Part #205165-1
RECEPT ASSY,25 POSN,AMPLIMITE



TE Part #085193P003
[ES1000-NO.4-B7-X-STK](#)



TE Part #176274-1
AMP UNIVERSAL POWER PLUG 6P



TE Part #YDTS26W15-35SNV001
D38999: Straight Plug, 15-35 Insert



TE Part #152435-000
CWT-5-W122-5



TE Part #2058128-2
Dust Cap, 4 Posn, Natural



TE Part #1393203-4
[V23148-A0003-A101](#)

Documents

Product Drawings

[CWT-6-W122-5](#)

English

Datasheets & Catalog Pages

[1654025_Sec8_B-155_CWT_D-110_D-1744](#)

English

[Raychem Electrical Interconnect Products](#)

English



Product Specifications

Product Specification

English

SolderSleeve One-Step Wire and Cable Terminators Installation Procedures for CWT and B-155 Products

English