TC6-09-PFH ✔ ACTIVE

Buchanan

TE Internal #: 4-1437661-2

Barrier Strips, 9 Position, 9.53mm [.375in] Centerline, 1 Row

View on TE.com >

Connectors > Terminal Blocks & Strips > Barrier Strips



Number of Positions: **9**

Centerline (Pitch): **9.53 mm [.375 in]**

Number of Rows: **1**

Features

Product Type Features

Product Type	Barrier Strip

Configuration Features

Number of Positions	9
Number of Rows	1

Body Features

Color	Black

Housing Features

Housing Material	Thermoplastic
Centerline (Pitch)	9.53 mm[.375 in]

Industry Standards

UL Flammability Rating	UL 94V-0

Packaging Features

Packaging Method	Package
Packaging Quantity	1

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold

EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JAN 2021 (211) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: https://echa.europa.eu/guidance-documents/guidance-on-reach

Compatible Parts



TE Part # 3-1437661-4
TC6-05-PFH=COVER w/HOLES



TE Part # 4-1437661-4
TC6-10-PFH=COVER w/HOLES



TE Part # 1437661-1
11S-SOCKET=11S SOCKET



TE Part # 2-1546686-4
6PCV-09-009=#6 TRIBARRIER



TE Part # 4-1437661-5
TC6-12-PFH=COVER w/HOLES

Customers Also Bought



TE Part #3-1879354-9
RR03 5% 12R AMMO



TE Part #2-323934-2
T-SHIELD,SN,GREEN,.115-.130



TE Part #390319-000
Heat Shrink Shielded Cable Splice Kit



TE Part #2-1375820-4
Receptacle Housing: 2.54mm, 1 Row, CST-100 II



TE Part #2273040-3
M12 A-CODE MALE STRAIGHT PIGTAIL



TE Part #EB0177-000
HVS-C-SJ IN-LINE HEAT SHRINK SPLICES



TE Part #216936-000
Medium-Wall Heat Shrink Tubing



TE Part #3-1658527-2
622-6441LF=FSKT IDC S 64 30AU



TE Part #2-380937-0
MR SPLT GROMET .312 DIA BLK LF

Documents

Product Drawings

TC6-09-PFH=COVER w/HOLES

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_4-1437661-2_C.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_4-1437661-2_C.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_4-1437661-2_C.3d_stp.zip

English

By downloading the CAD file I accept and agree to the Terms and Conditions of use.

Datasheets & Catalog Pages

BUCHANAN TERMINAL BLOCKS CATALOG - BARRIER STRIPS

English

Product Environmental Compliance

TE Material Declaration

English