




Connectors > Rectangular Connectors > Rectangular Connector Accessories > Rectangular Caps & Covers



Protection & Strain Relief Accessory Type: **Strain Relief Coverpart Kit**

Connector System: **Cable-to-Cable**

Number of Positions: **8**

Sealable: **No**

Connector & Contact Terminates To: **Wire & Cable**

Features

Product Type Features

Protection & Strain Relief Accessory Type	Strain Relief Coverpart Kit
Connector System	Cable-to-Cable
Sealable	No
Connector & Contact Terminates To	Wire & Cable

Configuration Features

Number of Positions	8
---------------------	---

Usage Conditions

Operating Temperature Range	-20 – 85 °C[-4 – 185 °F]
-----------------------------	--------------------------

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	



Current ECHA Candidate List: JAN 2021
(211)
Candidate List Declared Against: JAN 2017
(173)
SVHC > Threshold:
Not Yet Reviewed

Halogen Content	BFR/CFR/PVC Free, but Br/Cl >900 ppm in other sources.
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulations, TE’s information on SVHC in articles for this part number is still based on the European Chemical Agency (ECHA) ‘Guidance on requirements for substances in articles’(Version: 2, April 2011), applying the 0.1% weight on weight concentration threshold at the finished product level. TE is aware of the European Court of Justice ruling of September 10th, 2015 also known as O5A (Once An Article Always An Article) stating that, in case of ‘complex object’, the threshold for a SVHC must be applied to both the product as a whole and simultaneously to each of the articles forming part of its composition. TE has evaluated this ruling based on the new ECHA “Guidance on requirements for substances in articles” (June 2017, version 4.0) and will be updating its statements accordingly.

Compatible Parts

TE Part # 794617-8
8POS,MICRO MNL,RCPT HSG

Customers Also Bought

TE Part #2213678-4
Z35 MINI LED HOLDERS

TE Part #1833011-1
STD SCHRACK RZF Power Relays

TE Part #2213933-2
Surface Mount TB Headers


TE Part #1-794608-1
PIN CONT 20-24 15 GOLD STRIP



TE Part #1-794611-1
MICRO MNL RPT CNT,LS PC,15AU,L



TE Part #1-794612-0
PIN CONT 20-24 TIN PLATE L/P



TE Part #1-282834-1
TERMI-BLOK PCB MOUNT, 90 11P.



TE Part #104935-2
08 MTE HDR SRRA LATCH



TE Part #1-794616-6
FREE HANG DBL ROW HSG 16 POS



TE Part #YAFD56-16-26PNC012
PLUG ASSY

Documents

Product Drawings

8 pos. coverpart (kit) for P/N 794616-8

English

Product Specifications

Application Specification

English