




Connectors > Audio & Video Connectors > USB Connectors



USB Connector Type: **B**

USB Version: **2.0**

Connector Profile: **Standard**

Connector & Housing Type: **Receptacle**

Number of Ports: **1**

Features

Product Type Features

Integral Locking Latch	Without
USB Connector Type	B
USB Version	2.0
Connector & Housing Type	Receptacle
Connector System	Cable-to-Board
Connector & Contact Terminates To	Printed Circuit Board
Product Type	Connector
LED	Without

Configuration Features

Number of Ports	1
Number of Positions	4

Body Features

Offset	0 mm
Shell Plating Finish	Matte
Connector Profile	Standard



Shell Plating Material	Nickel
------------------------	--------

Contact Features

Contact Current Rating (Max)	1 A
Contact Mating Area Plating Material	Gold Flash over Palladium Nickel
Contact Mating Area Plating Thickness	.76 μm [29.92 μin]

Termination Features

Termination Method to Printed Circuit Board	Through Hole - Solder
---	-----------------------

Mechanical Attachment

Locking Feature	With
Locating Posts	Without
PCB Mount Location	Top
PCB Connector Seating	Flush
PCB Mount Retention Type	Straight Leg
Connector Mounting Type	Board Mount

Housing Features

Body Orientation	Right Angle
Centerline (Pitch)	2.5 mm[.098 in]
Housing Material	Thermoplastic
Housing Color	Black

Dimensions

Tail Length	3.01 mm[.119 in]
PCB Thickness (Recommended)	1.57 mm[.062 in]

Usage Conditions

Soldering Temperature (Max)	260 °C[500 °F]
Mating Cycles (Max)	1500
Operating Temperature Range	-55 – 85 °C[-67 – 185 °F]

Operation/Application

Halogen Free	No
Circuit Application	Signal

Industry Standards

Test Identification (TID)	60001136
Moisture Sensitivity Level	1



Industry Standard	USB 2.0
UL Flammability Rating	UL 94V-0

Packaging Features

Packaging Method	Box & Tray, Tray
Packaging Quantity	273

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JAN 2021 (211) Does not contain REACH SVHC
Halogen Content	Low Bromine/Chlorine - Br and Cl < 900 ppm per homogenous material. Also BFR /CFR/PVC Free
Solder Process Capability	Wave solder capable to 265°C

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Customers Also Bought



TE Part #1658610-3
IDC D-Sub: Receptacle Assembly, Low Profile, Signal, 2.77 mm




TE Part #1761608-3
IDC LOW PRO HDR 10P VERT SHT L



TE Part #1393776-4
V23026D1022B201 *X020



TE Part #1376164-1
BATTERY HOLDER ML621 ASSY



TE Part #1-2201196-0
0.4 STACKING CONN H0.98 PLUG ASSEMBLY




TE Part #1-1734035-1
MINI USB, TYPE B, R/A, SMT



TE Part #1437624-6
PK50B1/4=KNOB PLASTIC BLK 1/4



TE Part #DTP13-4P
DEUTSCH DTP HEADERS



TE Part #1-2201197-0
0.4 STACKING CONN H0.98 REC ASSEMBLY



TE Part #1-1734264-1
M/J,RJ45,Side entry,8P8C,R/A,1

Documents

Product Drawings

[STD USB TYPE B, R/A, T/H](#)

English

CAD Files

[3D PDF](#)

3D

Customer View Model

[ENG_CVM_CVM_292317-4_C.2d_dxf.zip](#)

English

Customer View Model

[ENG_CVM_CVM_292317-4_C.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_292317-4_C.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications



Application Specification

English

Product Environmental Compliance

[MD_292317-4_09112013523_dmtec](#)

English

[MD_292317-4_09112013523_dmtec](#)

English

Agency Approvals

[UL Report](#)

English