



Connectors > Automotive Connectors > Connector Accessories > Other Connector Accessories > LEAVYSEAL MOUNTING ACCESSORIES



Automotive Connector Accessory Type: **Alignment Plate**

Connector System: **Wire-to-Board, Wire-to-Wire**

Primary Product Material: **PBT GF**

Primary Product Color: **Black**

Number of Positions: **15, 22**

All LEAVYSEAL MOUNTING ACCESSORIES (8)

Features

Product Type Features

|                                     |                             |
|-------------------------------------|-----------------------------|
| Automotive Connector Accessory Type | Alignment Plate             |
| Connector System                    | Wire-to-Board, Wire-to-Wire |

Configuration Features

|                     |        |
|---------------------|--------|
| Number of Positions | 15, 22 |
|---------------------|--------|

Body Features

|                          |        |
|--------------------------|--------|
| Primary Product Material | PBT GF |
| Primary Product Color    | Black  |

Usage Conditions

|                             |                            |
|-----------------------------|----------------------------|
| Operating Temperature Range | -40 – 140 °C[-40 – 284 °F] |
|-----------------------------|----------------------------|

Industry Standards

|                        |          |
|------------------------|----------|
| UL Flammability Rating | UL 94-HB |
|------------------------|----------|

Packaging Features

|                    |     |
|--------------------|-----|
| Packaging Quantity | 112 |
| Packaging Method   | Box |

Other

|             |     |
|-------------|-----|
| Serviceable | Yes |
|-------------|-----|



Product Compliance


For compliance documentation, visit the product page on TE.com>

|                                               |                                                                                                                               |
|-----------------------------------------------|-------------------------------------------------------------------------------------------------------------------------------|
| EU RoHS Directive 2011/65/EU                  | Compliant                                                                                                                     |
| EU ELV Directive 2000/53/EC                   | Compliant                                                                                                                     |
| China RoHS 2 Directive MIIT Order No 32, 2016 | No Restricted Materials Above Threshold                                                                                       |
| EU REACH Regulation (EC) No. 1907/2006        | Current ECHA Candidate List: JAN 2021 (211)<br>Candidate List Declared Against: JAN 2021 (211)<br>Does not contain REACH SVHC |
| Halogen Content                               | Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free                                           |
| Solder Process Capability                     | Not applicable for solder process capability                                                                                  |

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



Also in the Series | LEAVYSEAL



Automotive Connector Caps & Covers (16)



Automotive Headers(13)



Automotive Housings(63)



Insertion & Extraction Tools(5)



Other Automotive Connector Accessories(15)

Customers Also Bought



TE Part #SGD-120-3  
CABLE ACTUATED POSITION STOCK LIST



TE Part #1614986-1  
LR0204 1% 120R



TE Part #1-1879027-0  
YR1 0.1% 60R4




TE Part #1-1823449-1  
LEAVYSEAL HOUSINGS



TE Part #1564562-2  
HEAVY DUTY CONNECTORS FIXING SLIDES



TE Part #1579007-8  
EXTRACTION TOOL



TE Part #1355437-3  
MCP9,5 EINZELDICHTG

Documents

Product Drawings  
ADAPTER,SEALED,ASSY

English

CAD Files  
Customer View Model  
ENG\_CVM\_1703806-1\_C.3d\_igs.zip

English

Customer View Model





[ENG\\_CVM\\_1703806-1\\_C.3d\\_stp.zip](#)

English

Customer View Model

[ENG\\_CVM\\_1703806-1\\_C.2d\\_dxf.zip](#)

English

3D PDF

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

CONNECTOR SELECTOR

English

Product Specifications

Application Specification

German