




Application Tooling > Insertion & Extraction Tools



Insertion & Extraction Tool Type: **Contact Extraction**
Insertion & Extraction Tool Application: **Contact-to-Housing**

Features

Product Type Features

Insertion & Extraction Tool Type	Contact Extraction
Insertion & Extraction Tool Application	Contact-to-Housing

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Out of Scope
EU ELV Directive 2000/53/EC	Out of Scope
China RoHS 2 Directive MIIT Order No 32, 2016	Not reviewed for China RoHS compliance
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JUN 2016 (169) SVHC > Threshold: Not Yet Reviewed
Halogen Content	Not Yet Reviewed for halogen content
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulations, TE's information on SVHC in articles for this part number is still based on the European Chemical Agency (ECHA) 'Guidance on requirements for



substances in articles’(Version: 2, April 2011), applying the 0.1% weight on weight concentration threshold at the finished product level. TE is aware of the European Court of Justice ruling of September 10th, 2015 also known as O5A (Once An Article Always An Article) stating that, in case of ‘complex object’, the threshold for a SVHC must be applied to both the product as a whole and simultaneously to each of the articles forming part of its composition. TE has evaluated this ruling based on the new ECHA “Guidance on requirements for substances in articles” (June 2017, version 4.0) and will be updating its statements accordingly.

Compatible Parts

 TE Part # CAT-SI261-C1701A Glow Wire Signal Double Lock Cap	 TE Part # CAT-SI261-P729A Glow Wire Signal Double Lock Plug	 TE Part # CAT-SI261-C1701 STD Temp Signal Double Lock Cap	 TE Part # CAT-SI261-P729 STD Temp Signal Double Lock Plug
 TE Part # CAT-SI261-T669 Signal Double Lock TPA	 TE Part # CAT-SI261-T111 Signal Double Lock Tab	 TE Part # CAT-SI261-R2435 Signal Double Lock Receptacle	 TE Part # 917701-1 2.5 SIGNAL DBL LOCK DLP 5P
 TE Part # 5-917690-1 2.5 SIGNAL D/LOCK PLUG HSG 6P	 TE Part # 316398-1 2.5 SIGNAL D/L TAB CONT. L L/P	 TE Part # 316399-1 2.5 SIGNAL D/L TAB CONT. M L/P	 TE Part # 316401-1 2.5 SIGNAL D/L REC CONT. M L/P
 TE Part # 316094-2 2.5 S.D.L. CAP HSG 10P RED	 TE Part # 5-917696-1 2.5 SIGNAL D/LOCK PLUG HSG 12P	 TE Part # 9-917684-1 2.5 SGL DBL LOCK REC CONT	 TE Part # 917688-6 SIGNAL DOUBLE LOCK PLUG HSG 4P BLUE



TE Part # 917694-2
2.5 S.D.L. PLUG HSG 10P RED

TE Part # 5-917698-1
2.5 SIGNAL DBL LOCK D.L.P 2P

TE Part # 917687-6
2.5 SIGNAL D/LOCK PLUG HSG 3P

TE Part # 917693-4
2.5 S.D.L. PLUG HSG 9P YELLOW

Also in the Series | AMP Signal Double Lock

Connector Contacts(9)

Insertion & Extraction Tools(1)

PCB Connector Seals(1)

PCB Latches, Locks & Retainers(17)

Rectangular Caps & Covers(1)

Rectangular Connector Housings(23)

Rectangular Connector Locking(2)

Rectangular Connector Seals(10)

Rectangular Power Connectors(3)

Standard Rectangular Connectors(1)

Wire-to-Board Connector Assemblies & Housings(74)

Wire-to-Board Connector Contacts(6)

Wire-to-Board Headers & Receptacles (157)

Customers Also Bought



TE Part #917781-1
2.5 S.D.L POST/HDR ASY 3P STD

TE Part #2-173985-9
AMP CT MT AMP-IN HDR-V BLU 9P

TE Part #2-179861-1
STD Temp Power Double Lock Plug

TE Part #2-1903391-3
STD Temp Sig GRACE INERTIA Cap

TE Part #3-1903388-4
STD Temp Sig GRACE INERTIA Plug

TE Part #176448-6
POSITIVE LOCK 187 (4.8 MM)
HOUSING

TE Part #1318558-1
SMARTEC SPRING LOCK LEVER ASSY

TE Part #1729279-1
EXTRACTION TOOL FOR GIC 3.5
CONN.

TE Part #353256-1
110 HSG. PL EX REC. 7.6mm 3P NAT

Documents

Instruction Sheets

EXTRACTION TOOL FOR AMP* SIGNAL DOUBLE LOCK CONNECTOR 234605-1

English

Instruction Sheet (non U.S.)

English