2295892-1 ✔ ACTIVE

MotorMan



TE Internal #: 2295892-1

MotorMan, Rectangular Caps & Covers, Shroud, Compatible With Connector Shell Size 48, Plug, Operating Temperature Range -20 – 85 °C [-4 – 185 °F]

View on TE.com >

Connectors > Rectangular Connectors > Rectangular Connector Accessories > Rectangular Caps & Covers



Protection & Strain Relief Accessory Type: **Shroud**

Compatible With Connector Shell Size: **48**

Compatible With Connector Style: **Plug**

Operating Temperature Range: **-20 – 85 °C [-4 – 185 °F]**

UL Flammability Rating: **UL 94V-0**

Features

Product Type Features

Accessory Color	Black
Product Type	Accessory
Protection & Strain Relief Accessory Type	Shroud

Body Features

Color	Black
Material	PA66

Dimensions

Length	45.6 mm
Width	29.6 mm
Height	14 mm

Usage Conditions

Compatible With Connector Style	Plug
Operating Temperature Range	-20 – 85 °C[-4 – 185 °F]

Operation/Application

For Use With	Plug housing
Compatible With Connector Shell Size	48

Industry Standards

UL Flammability Rating	UL 94V-0

Packaging Features

Packaging Method	Bag/Box
Packaging Quantity	10

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JUN 2016 (169) SVHC > Threshold: Not Yet Reviewed
Halogen Content	Not Yet Reviewed for halogen content
Solder Process Capability	Not reviewed for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: https://echa.europa.eu/guidance-documents/guidance-on-reach

Compatible Parts




TE Part # 2295891-1
SCREEN CLAMP; MOTORMAN SHROUD



TE Part # 2295895-1
SIDE CLIP, PLASTIC

Also in the Series | MotorMan



Circular Connector Caps & Covers(1)



Circular Connector Contact Inserts(2)



Circular Connector Seals(1)



Rectangular Backshells & Clamps(3)



Rectangular Caps & Covers(1)



Rectangular Connector Hardware(2)



Rectangular Connector Hoods & Bases (4)



Rectangular Connector Locking(2)



Rectangular Connector Seals(1)



Rectangular Contact Inserts(5)




Rectangular Power Connectors(2)

Customers Also Bought



TE Part #2295893-1
MALE INSERT HOUSING



TE Part #2295894-1
SIGNAL HOUSING




TE Part #2120325-1
TAB CONNECTOR



TE Part #2120320-1
FEMALE INSERT WITH PE-CONTACT



TE Part #1245276-2
HG-Q-Buegel-100



TE Part #878630-000
Bulbous Heat Shrink Boots: Lipped, Straight



TE Part #1103426-2
MALE INSERT, CRIMP, 4-POS. 22DF CONTACTS



TE Part #2120340-1
PLASTIC HOOD / KIT



TE Part #2266429-1
OC-AT-S-FM-062F090F-001-0426



TE Part #2295897-1
FLANGE SEALING

Documents

Product Drawings

SHROUD PLASTIC

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_2295892-1_A.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_2295892-1_A.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_2295892-1_A.3d_stp.zip

English

By downloading the CAD file I accept and agree to the Terms and Conditions of use.

Product Specifications

Product Specification

English