



Connectors > Modular Jacks & Plugs > Modular Jack & Plug Accessories > Modular Jack & Plug Caps & Covers



Modular Jacks & Plugs Accessory Type: **Stuffer Cap**

Modular Jacks & Plugs Products: **Accessories**

Number of Positions: **6**

Centerline (Pitch): **2.16 mm [.085 in]**

Sealable: **No**

Features

Product Type Features

Modular Jacks & Plugs Accessory Type	Stuffer Cap
Modular Jacks & Plugs Products	Accessories
Sealable	No

Configuration Features

Number of Positions	6
---------------------	---

Housing Features

Centerline (Pitch)	2.16 mm[.085 in]
--------------------	------------------

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Not Yet Reviewed




Halogen Content	Not Yet Reviewed for halogen content
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulations, TE’s information on SVHC in articles for this part number is still based on the European Chemical Agency (ECHA) ‘Guidance on requirements for substances in articles’(Version: 2, April 2011), applying the 0.1% weight on weight concentration threshold at the finished product level. TE is aware of the European Court of Justice ruling of September 10th, 2015 also known as O5A (Once An Article Always An Article) stating that, in case of ‘complex object’, the threshold for a SVHC must be applied to both the product as a whole and simultaneously to each of the articles forming part of its composition. TE has evaluated this ruling based on the new ECHA “Guidance on requirements for substances in articles” (June 2017, version 4.0) and will be updating its statements accordingly.

Compatible Parts



TE Part # 216000-2
6P. TOOLLESS MOD J.

Customers Also Bought



TE Part #10202023-00
Pressure Transducers Readily Available




TE Part #2273095-2
M12 A-CODE FEMALE R/A PIGTAIL



TE Part #T4162213005-005
M12 A-CODE MR-FS DOUBLE ENDED CABLE




TE Part #2-796949-5
25POS TERMI-BLOK PCB MOUNT



TE Part #1-282856-1
11P TERMI-BLOK PCB MOUNT



TE Part #1-796690-1
TERMI-BLOK PCB MOUNT 11P



TE Part #2329383-7
PB OFF/ON FC RED M2 TERM. IP68



TE Part #102692-1
12 MODII 2PC HDR DR SHRD



TE Part #1571551-4
DIP Socket: Standard, Stamped & Formed, Closed, Tin

Documents

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_216003-2_B.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_216003-2_B.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_216003-2_B.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.