1-350373-9 ✔ ACTIVE

AMP

TE Internal #: 1-350373-9

Rectangular Boots & Strain Relief, Strain Relief, Nylon, Black, 6 Position, Operating Temperature Range -55 – 85 °C [-67 – 185 °F]

View on TE.com >

Connectors > Rectangular Connectors > Rectangular Connector Accessories > Rectangular Boots & Strain Relief



Protection & Strain Relief Accessory Type: **Strain Relief**

Primary Product Material: **Nylon**

Primary Product Color: **Black**

Number of Positions: **6**

Sealable: **No**

Features

Product Type Features

Protection & Strain Relief Accessory Type	Strain Relief
Sealable	No
Product Type	Accessory

Configuration Features

Number of Positions	6

Body Features

Primary Product Material	Nylon
Primary Product Color	Black

Usage Conditions

Operating Temperature Range	-55 – 85 °C[-67 – 185 °F]

Industry Standards

Agency/Standard	CSA, UL

Packaging Features

Packaging Method	Box
Packaging Quantity	100

Other

Comment	One piece - Clam Shell.

Product Compliance


For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JAN 2021 (211) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer


This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: https://echa.europa.eu/guidance-documents/guidance-on-reach

Compatible Parts




TE Part # 1-640520-0
06P MR II PLUG HSG V0 RED


Customers Also Bought



TE Part #1-640508-0
03P MR II CAP HSG V0 RED




TE Part #1-640510-0
06P MR II CAP HSG V0 RED



TE Part #1-640520-0
06P MR II PLUG HSG V0 RED



TE Part #1318912-1
EP CONN LP REC



TE Part #1-350522-9
09P MR STR/REL HNG BLK




TE Part #1-6609005-2
CORCOM EEB SERIES IEC FILTERED INLETS



TE Part #1-51692-6
N SERIES PLUG RG 217



TE Part #8-1437572-2
TPF13C0=PUSHBUTTON SWITCH



TE Part #1-350374-9
12P STR/REL HNGD



TE Part #1-350523-9
15P MR STR/REL HNG BLK

Documents

Product Drawings

06P STR/REL HNGD

English

CAD Files

Customer View Model

ENG_CVM_1-350373-9_K.3d_igs.zip

English

Customer View Model

ENG_CVM_1-350373-9_K.3d_stp.zip

English

Customer View Model

ENG_CVM_1-350373-9_K.2d_dxf.zip

English

3D PDF

English

By downloading the CAD file I accept and agree to the Terms and Conditions of use.

Datasheets & Catalog Pages

SOFT_SHELL_PIN_AND_SOCKET_CONNECTORS_CATALOG

English

Product Specifications

Application Specification

English

Instruction Sheets

Instruction Sheet (U.S.)

English

AMP* MINIATURE RECTANGULAR II (MRII) CONNECTORS

English