



Application Tooling > Insertion & Extraction Tools



Insertion & Extraction Tool Type: **Contact Extraction**
Insertion & Extraction Tool Application: **Contact-to-Wire**

Features

Product Type Features

Insertion & Extraction Tool Type	Contact Extraction
Insertion & Extraction Tool Application	Contact-to-Wire

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Not Compliant
EU ELV Directive 2000/53/EC	Out of Scope
China RoHS 2 Directive MIIT Order No 32, 2016	Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JUN 2020 (209) SVHC > Threshold: Pb (3% in Component Part) Article Safe Usage Statements: Do not eat, drink or smoke when using this product. Wash thoroughly after handling. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location.
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability


Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products



will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

 TE Part # CAT-R7602-T273 ROUND CONNECTOR SYSTEM, PIN AND SOCKET	TE Part # 1703420-5 DIA 4MM CON	TE Part # 3-965867-1 ABS4MM BU REPAR-KIT	TE Part # 962953-1 4MM SOCKET CONTACT SWS LOOSE PIECE
TE Part # 962955-1 4MM SOCK.CONT.(LP)	TE Part # 962955-5 4MM BUCHS-KONTAKT	TE Part # 962957-1 4MM BU-KONTAKT EDS	TE Part # 962957-2 4MM BU-KONTAKT EDS
TE Part # 965840-1 4MM BUCHSENKONTAKT	TE Part # 965867-1 4MM SOCKET CONTACT	TE Part # 965868-1 4MM SOCKET CONTACT	 TE Part # 962955-2 4MM RECEPTACLE CONTACT SWS (1,0-2,5MM?)
TE Part # 1703420-2 DIA 4MM CON	 TE Part # 6-962952-6 4MM BUCHS-KONTAKT	TE Part # 962953-2 4MM SOCKET CONTACT SWS	

Also in the Series | Round Connector System



Automotive Connector Caps & Covers (5)



Automotive Housings(16)



Automotive Seals & Cavity Plugs(3)



Automotive Terminals(77)




Insertion & Extraction Tools(8)

Customers Also Bought



TE Part #SRK06-FLA-64A-001
DEUTSCH STRIKE HOUSINGS



TE Part #1276565-1
EXTRACTION TOOL FOR .025 REC



TE Part #1-967628-4
TIMER, CONNECTOR HOUSING




TE Part #1-963734-1
TIMER, RECEPTACLE AND TAB




TE Part #1-963540-1
SIGNAL HEADER




TE Part #1379118-2
MQS, CONNECTOR HOUSING



TE Part #1333204-4
ANVIL



TE Part #1333204-5
ANVIL,COMBINATION .080



TE Part #1333205-4
ANVIL, COMBINATION (.090)



TE Part #1366865-1
EXT-TOOL FOR 025 TAB

Documents



Datasheets & Catalog Pages

Insertion-Extraction-Tool-2345721-1

English

Crimp Term Whitepaper-Use the Right Tool 1-1773953-1

English

CRIMPING WHERE FORM MEETS FUNCTION

English