



Application Tooling > Insertion & Extraction Tools



Insertion & Extraction Tool Type: **Contact Extraction**

Insertion & Extraction Tool Application: **Contact-to-Wire**

Features

Product Type Features

Insertion & Extraction Tool Type	Contact Extraction
Insertion & Extraction Tool Application	Contact-to-Wire

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JUN 2020 (209) SVHC > Threshold: Not Yet Reviewed
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous



materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts





 TE Part # 1-1105251-1 HSM-C-Bu.Ag.0,75 qmm	 TE Part # 4-1105250-1 HSM-C-Sti.Ag.4 qmm	 TE Part # 4-1105251-1 HSM-C-Bu.Ag.4 qmm	 TE Part # 6-1105251-1 HSM-C-Bu.Ag.10 qmm
 TE Part # 1-1105250-1 HSM-C-Sti.Ag.0,75 qmm	 TE Part # 2-1105250-1 HSM-C-Sti.Ag.1,5 qmm	 TE Part # 2-1105251-1 HSM-C-Bu.Ag.1,5 qmm	 TE Part # 3-1105250-1 HSM-C-Sti.Ag.2,5 qmm
 TE Part # 3-1105251-1 HSM-C-Bu.Ag.2,5 qmm	 TE Part # 5-1105250-1 HSM-C-Sti.Ag.6 qmm	 TE Part # 5-1105251-1 HSM-C-Bu.Ag.6 qmm	 TE Part # 6-1105250-1 HSM-C-Sti.Ag.10 qmm

Also in the Series | HDC HD

 Connector Contacts(24)	 Insertion & Extraction Tools(5)	 Rectangular Contact Inserts(44)
---	--	--

Customers Also Bought



 TE Part #1102855-3 AWZG-HVT-RSZ	 TE Part #1-1105851-8 RSZ.HE-HND-HVT	 TE Part #1-1105850-8 RSZ.BAS	 TE Part #1102855-6 EWZG-RSZ
 TE Part #1102855-2 AWZG-HN.D-RSZ	 TE Part #1-1393224-8 RYA32024	 TE Part #1-1478052-0 BNC Pnl Plg 75Ohm Silver Pltd	 TE Part #1102855-1 AWZG-HD.M-RSZ
 TE Part #1102855-5 AWZG-HSS-RSZ	 TE Part #NDNOSP2842S0050 SP 2841 130 050 003		

Documents

Product Drawings
AWZG-HSM-RSZ

German

Datasheets & Catalog Pages
Insertion-Extraction-Tool-2345721-1

English

Crimp Term Whitepaper-Use the Right Tool 1-1773953-1

English

CRIMPING WHERE FORM MEETS FUNCTION

English