

TCM008PC1TT036BC

✓ ACTIVE

Nanonics | [CeeLok FAS-T Connector](#), [CeeLok FAS-T Nano Connector](#)


TE Internal #: 1925252-1

CeeLok FAS-T Connector, Standard Circular Connectors, Wire-to-Wire, 8 Position, Electroless Nickel, 3.5 Shell Size, Contacts Preloaded, Plug

[View on TE.com >](#)



Connectors > Circular Connectors > Standard Circular Connectors



Connector System: **Wire-to-Wire**
Number of Positions: **8**
Shell Plating Material: **Electroless Nickel**
Circular Connector Shell Size: **3.5**
Contacts Preloaded: **Yes**

Features

Product Type Features

Product Type	Connector
Connector System	Wire-to-Wire
Circular Connector Type	Plug

Configuration Features

Number of Positions	8
Contacts Preloaded	Yes

Signal Characteristics

Data Rate	10 Gb/s
-----------	---------

Body Features

Shell Plating Material	Electroless Nickel
------------------------	--------------------

Housing Features


Circular Connector Shell Size	3.5
-------------------------------	-----

Packaging Features

Packaging Quantity	1
--------------------	---

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)





EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JAN 2019 (197) SVHC > Threshold: Not Yet Reviewed
Halogen Content	Not Yet Reviewed for halogen content
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Also in the Series | CeeLok FAS-T Connector



Standard Circular Connectors(48)

Also in the Series | CeeLok FAS-T Nano Connector



Standard Circular Connectors(48)



Customers Also Bought



TE Part #2227581-1
Internal Mini-SAS HD Receptacles



TE Part #2016032-1
3 PORT QSL SMT W/O FLANGE, TH




TE Part #2302339-1
NanoRF SKT CONTACT, DAUGHTER CARD




TE Part #104693-8
80 50/50 HDR DRST SFMNT .390



TE Part #YDTS26W17-08BNV001
D38999: Straight Plug, 17-08 Insert



TE Part #1064544-1
9960 4100 02,CABLE ASSEMBLY



TE Part #1064560-1
9960 4305 01



TE Part #2302345-1
NanoRF PIN CONTACT, BACKPLANE



TE Part #2-2176072-0
CPF 0201 78R7 0.5% 25PPM 1K RL



TE Part #2-2176072-4
CPF 0201 86R6 0.5% 25PPM 1K RL

Documents

Product Drawings

TCM008PC1TT036BC = Circular

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_1925252-1_A_c-1925252-1-a.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_1925252-1_A_c-1925252-1-a.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_1925252-1_A_c-1925252-1-a.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.



Datasheets & Catalog Pages

Wire and Cable Overview

English

Product Specifications

Product Specification

English