



Terminals & Splices > Ring Terminals & Spade Terminals



Terminal & Splice Type: **Ring Tongue**

Wire Size: **201438 – 214928 CMA**

Ring & Spade Stud Size: **3/8**

Features

Product Type Features

Ring & Spade Stud Size	3/8
Ring & Spade Barrel Type	Closed Barrel
Sealable	Yes
Insulated	No
Ring & Spade Wire/Cable Type	Aluminum Wire
Support Style	Insulation Support

Configuration Features

Terminal Angle	Straight
----------------	----------

Body Features

Weight per Piece	37.736 g
Ring & Spade Plating Material	Tin

Contact Features

Terminal & Splice Type	Ring Tongue
Ring & Spade Terminal Orientation	Straight
Underplating Material	Nickel

Dimensions

Wire Size	201438 – 214928 CMA
Stud Diameter	9.91 mm[.39 in]
Tongue Thickness	6.86 mm[.27 in]



Ring & Spade Overall Length	78.99 mm[3.11 in]
Barrel Inside Diameter	18.59 mm[.732 in]
Ring & Spade Wire Insulation Diameter (Max)	17.34 mm[.683 in]
Ring & Spade Wire Insulation Diameter	14.99 – 17.35 mm[.59 – .683 in]

Usage Conditions

Insulation Requirement	Uninsulated
Operating Temperature Range	-65 – 175 °C[-85 – 347 °F]

Operation/Application

Heavy Duty	No
------------	----

Packaging Features

Ring & Spade Packaging Method	Box
-------------------------------	-----

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JUN 2020 (209) SVHC > Threshold: Not Yet Reviewed
Halogen Content	Out of Scope - excluded from Halogen requirements
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer


This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>



Compatible Parts



TE Part # 58422-1
HYP8 8-4/0AWG 33T HEAD




TE Part # 314948-3
DIE SET, 4/0 AL, W/ SUPPORTS



TE Part # 314948-4
DIE SET, 4/0 AL W/O SUPPORTS

Customers Also Bought



TE Part #CZ1868-000
Low Profile Heat Shrink Boots: Poly Mold, Lipped, Right Angle




TE Part #A80174-000
D-438-0104



TE Part #2102573-1
ASSY 2/0 AL COPALUM LITE SINGLE HOLE 3/8



TE Part #2102579-1
ASSY 2 AL COPALUM LITE DUAL HOLE 3/8




TE Part #314948-3
DIE SET, 4/0 AL, W/ SUPPORTS



TE Part #650124-000
D-436-94




TE Part #ZPF000000000163975
DMC-M 99-04 CN (=33537-PC000)



TE Part #ZPF00000000017870
FAST-E 01 M-X-B 00 A



TE Part #ZPF00000000018123
FDBA 50-14-19 PN-K 090 A231



TE Part #7449910001
TMS-SCE-1-2.0-S2-9

Documents

Product Drawings
ASSY 4/0 AL COPALUM LITE SINGLE HOLE 3/8

English

Datasheets & Catalog Pages
COPALUM Lite Sealed Terminals and Splices

English



Product Specifications

Application Specification

English

Instruction Sheets

Instruction Sheet (U.S.)

English