



Connectors > Circular Connectors > Circular Connector Accessories > Circular Connector Caps & Covers



Protection & Strain Relief Accessory Type: **Dust Cap**
Cap to Flange Attachment: **Push/Pull**
Number of Positions: **1**
Sealable: **No**
Connector Mounting Type: **Cable Mount (Free-Hanging)**

Features

Product Type Features

Connector Design	Circular
Product Type	Accessory
Connector Style	Receptacle
Protection & Strain Relief Accessory Type	Dust Cap
Sealable	No

Configuration Features

Number of Positions	1
---------------------	---

Body Features

Sealing Cap Plating Material	Black Chromate
Shell Finish	Black Chromate
Cap Material	Brass

Mechanical Attachment

Cap to Flange Attachment	Push/Pull
Connector Mounting Type	Cable Mount (Free-Hanging)

Dimensions

Panel Thickness	3 mm[.118 in]
-----------------	---------------

Usage Conditions

Operating Temperature Range	-55 – 125 °C[-67 – 257 °F]
-----------------------------	----------------------------



Operation/Application

For Use With	Receptacle Connector
--------------	----------------------

Packaging Features

Packaging Quantity	1
Packaging Method	Bag

Other

Comment	1
---------	---

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Not Yet Reviewed
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JAN 2019 (197) SVHC > Threshold: Not Yet Reviewed
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Hand solderable with tin/lead solder

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Customers Also Bought



TE Part #3-646547-0
Hard Metric Backplane Receptacle Connector: Mezzanine, 2mm

TE Part #1825533-1
14 MTE HDR SRST LATCH .100CL

TE Part #2-1658549-7
FPH-3222G=FLXPAC HDR P 32 ST LF

TE Part #646428-1
Z-PACK 2MM HM,TYPE D,L/SHEILD

TE Part #3-5331272-9
Mini Spring Sockets: Open Bottom, 4A

TE Part #YDTS20F25-04SEV001
D38999: Square Flange, 25-04 insert

TE Part #3-1888291-3
FPH-2021G=FLXPAC HDR P 20 ST L

TE Part #534286-9
26 MODIV VERT DR 100CL/SFMNT

TE Part #2101579-2
DUST CAP,RCPT,Sz105,F SERIES

Documents

Product Drawings
DUST CAP,RCPT,Sz3,F SERIES

English

Datasheets & Catalog Pages
Products for Aerospace and Defense

English

Product Specifications
Product Specification

English