



Connectors > Rectangular Connectors > Rectangular Connector Accessories > Rectangular Connector Hardware



Hardware Type: **Jackscrew Kit**
Jackscrew Type: **Turnable**
Jackscrew Style: **Female**
Connector System: **Wire-to-Wire**
Number of Positions: **12, 28, 42, 50, 75, 104**

Features

Product Type Features

Strain Relief	Without
Product Type	Hardware
Connector System	Wire-to-Wire
Sealable	No
Connector & Contact Terminates To	Wire & Cable

Configuration Features

Number of Positions	12, 28, 42, 50, 75, 104
---------------------	-------------------------

Body Features

Material	Stainless Steel, Zinc Alloy
Thread Lead Type	Single

Mechanical Attachment

Jackscrew Material	Zinc Alloy
Jackscrew Finish	Hexavalent Chromate
Mounting Hardware	Jackscrew Tip Female and Spirol Pin
Screw & Hole Thread Size	6-32 [M3.5 x .6]
Hardware Type	Jackscrew Kit
Jackscrew Type	Turnable
Jackscrew Style	Female



Connector Mounting Type	Cable Mount (Free-Hanging)
Dimensions	
Height	7.92 mm[.312 in]
Length	81.44 mm[3.206 in]
Width	7.92 mm[.312 in]
Usage Conditions	
Operating Temperature Range	-55 – 150 °C[-67 – 302 °F]
Operation/Application	
For Use With	12 Position High Current Connectors, 28 Position High Voltage Connectors, 42-Position Mixed Connectors, 50, 75 and 104-Position Standard Connectors
Circuit Application	Power & Signal
Packaging Features	
Packaging Quantity	1
Packaging Method	Bag
Other	
Comment	Two required., Use turnable jackscrews on mating housings when mating to grounding block.

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JAN 2021 (211) Does not contain REACH SVHC
Halogen Content	Not Yet Reviewed for halogen content
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as



EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 207234-1
UNASSM JS KIT,M SERIES



TE Part # 7-170995-1
JACK SCREW FEMALE



TE Part # 7-170995-2
JACK SCREW FEMALE ASSY



TE Part # 7-170995-3
M SERIES JACK SCREW ASSY

Also in the Series

AMP M Series



Board-to-Board Jumpers & Shunts(7)




Rack & Panel Connectors(1)



Rectangular Connector Hardware(52)



Rectangular Power Connectors(69)



Standard Edge Connectors(2)

Customers Also Bought




TE Part #1-51864-1
PIDG RING TONGUE TERMINALS




TE Part #130552
SOLIS 6 R M5



TE Part #1-201046-2
SERIES "M" MIN RECT GUIDE PIN



TE Part #1586315-4
VAL-U-LOK SKT PHBZ AU 24-18 LP



TE Part #150492
DG 22-16COM 22-18MIL HR R M3.5



TE Part #1-2176331-9
CRGP 2512 330R 1%



TE Part #E21108-000
HX-SCE LOW FIRE HAZARD SLEEVES



TE Part #1757828-2
AMPLIMITE,RCPT ASY,POSTD,109,ZN, 2



TE Part #1757828-3
AMPLIMITE,RCPT ASY,POSTD,109,ZN, 3



TE Part #1757828-4
AMPLIMITE,RCPT ASY,POSTD,109,ZN, 4

Documents

Product Drawings
UNASSM JS KIT,M SERIES

English

CAD Files
Customer View Model
ENG_CVM_207235-1_B1.3d_igs.zip

English

Customer View Model
ENG_CVM_207235-1_B1.3d_stp.zip

English

Customer View Model
ENG_CVM_207235-1_B1.2d_dxf.zip

English

3D PDF

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages



M_SERIES_PIN_AND_SOCKET_CONNECTORS

English