




Connectors > Circular Connectors > Circular Connector Accessories > Circular Connector Keying Plugs



Compatible With Connector Cavity Type: **Pin Cavities**
Sealable: **No**
Circuit Application: **Power**
Operating Temperature Range: **-55 – 105 °C [-67 – 221 °F]**

Features

Product Type Features

Product Type	Accessory
Accessory Type	Keying Plug
Sealable	No

Body Features

Keying Plug Color	Natural (White)
-------------------	-----------------

Usage Conditions

Operating Temperature Range	-55 – 105 °C[-67 – 221 °F]
-----------------------------	----------------------------

Operation/Application

Compatible With Connector Cavity Type	Pin Cavities
Circuit Application	Power

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JAN 2021 (211) Does not contain REACH SVHC



Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

TE Part # CAT-AM71-C83998BB
CPC SERIES 3

TE Part # CAT-AM71-C83998CC
CPC SERIES 4

TE Part # 207597-1
PLUG, TYPE XII KEYING

Also in the Series | AMP CPC

Circular Connector Adapters(7)

Circular Connector Boots & Strain Relief(6)

Circular Connector Caps & Covers(16)


Circular Connector Hardware(3)

Circular Connector Keying Plugs(2)


Circular Connector Seals(36)

Circular Power Connectors(513)

Insertion & Extraction Tools(1)



Power Contacts(5)



Sealing Sleeves(2)



Unscreened Circular Connector Backshells & Clamps(56)

Customers Also Bought



TE Part #206227-1
CPC SERIES 3




TE Part #T4171010004-001
M12 Panel Mount Wire



TE Part #1-747299-6
D-Sub Receptacle Assembly: Vertical, Shell Size 2, 2.74mm




TE Part #193991-4
PIN ASSY. TPE XII



TE Part #2-640497-2
02P MR HDR ASSY



TE Part #193990-2
SKT ASSY,TYPE XII, #8 AWG



TE Part #103186-2
04 MODII HDR DRST B/A .100CL



TE Part #1986377-2
CPC PSTD RCPT,13-7, rev sex



TE Part #1648162-1
261-0006-01100

Documents

Product Drawings
TYPE XII KEYING PLUG

English

CAD Files
3D PDF

English

Customer View Model
ENG_CVM_206508-1_D.2d_dxf.zip



English

Customer View Model

ENG_CVM_206508-1_D.3d_igs.zip

English

Customer View Model

ENG_CVM_206508-1_D.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

M_SERIES_PIN_AND_SOCKET_CONNECTORS

English

Instruction Sheets

Instruction Sheet (U.S.)

English

Agency Approvals

CSA Certificate

English