

TXR15AZ00-1010BI

✓ ACTIVE

Raychem | Raychem TXR

TE Internal #: CW3895-000

Raychem TXR, Ruggedized Backshells & Adapters, Connector
General Specification Number AS50151 Solder Contact with
ENDBELL, Aluminum

[View on TE.com >](#)



Connectors > Connector Backshells & Adapters > Ruggedized Backshells & Adapters



Connector General Specification Number: **AS50151 Solder Contact with ENDBELL**

Backshell Material: **Aluminum**

Adapter Plating Material: **Zinc Nickel (ASTM B841)**

Cable Diameter Range: **7.9 – 12.7 mm [.313 – .5 in]**

Adapter Angle: **Straight**

Features

Product Type Features

Termination Device Included	TR10BI
Pluggable I/O Accessory Type	Tinel-Lock Adapter
Adapter Angle	Straight
Termination Device Type	Side-Entry Tinel-Lock Ring, Tinel-Lock Adapter, Tinel-Lock Ring
Connector Shell Size	18, 19

Body Features

Color	Black
Backshell Material	Aluminum
Adapter Plating Material	Zinc Nickel (ASTM B841)
TE Adapter Code	15
Adapter Entry Size	10

Termination Features

Overbraid Termination	Tinel-Lock Ring
-----------------------	-----------------

Dimensions

Cable Entry Diameter	.2 – 15.9 mm[.01 – .63 in]
Cable Diameter Range	7.9 – 12.7 mm[.313 – .5 in]

Usage Conditions

Salt Spray Resistance	500 Hr
Operating Temperature Range	-65 – 175 °C[-85 – 347 °F]

Industry Standards

Connector Detail Specification Number	AS31001, AS31011, AS31061, AS31071, AS31081
---------------------------------------	---

Other

Connector General Specification Number	AS50151 Solder Contact with ENDBELL
--	-------------------------------------

Product Compliance


For compliance documentation, visit the product page on [TE.com](#)>

EU RoHS Directive 2011/65/EU	Compliant with Exemptions
EU ELV Directive 2000/53/EC	Compliant with Exemptions
China RoHS 2 Directive MIIT Order No 32, 2016	Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JAN 2021 (211) SVHC > Threshold: Pb (.3% in BODY & NUT) Article Safe Usage Statements: Do not eat, drink or smoke when using this product. Wash thoroughly after handling. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location.
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability


Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>


Compatible Parts



Also in the Series | Raychem TXR



Customers Also Bought





Documents

Product Drawings

TXR15AZ00-1010BI

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_CW3895-000_3.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_CW3895-000_3.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_CW3895-000_3.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

5-1654025-5_sec6_Adapters

English

Circular Backshells

English

Product Specifications

General Information Package for Tinel-Lock Adapters

English

Braid termination using a Tinel Lock Ring installed using a resistance heater.

English

PERFORMANCE SPECIFICATION Tinel-Lock Rings, Heat Recoverable for Braid Termination

English

ASSEMBLY GUIDE for Tinel -Lock Rings, Heat Recoverable for Braid Temination

English

Braid termination using a Tinel Lock Ring installed using a resistance heater.

French

Instruction Sheets

Instruction Sheet (U.S.)

English