




Connectors > PCB Connectors > Board-to-Board Connectors > PCB Spring Contacts



Spring Finger Type: **Preloaded - C-Clip**

Scalable: **No**

Side Protected: **No**

Uncompressed Height: **1.8 mm [.071 in]**

Contact Length: **3.46 mm [.136 in]**

Features

Product Type Features

Spring Finger Type	Preloaded - C-Clip
Scalable	No
Connector System	Board-to-Board
Sealable	No
Connector & Contact Terminates To	Printed Circuit Board

Configuration Features

Side Protected	No
Number of Positions	1

Contact Features

Contact Underplating Material	Nickel
PCB Contact Termination Area Plating Material	Gold
Contact Base Material	Stainless Steel
Contact Length	3.46 mm[.136 in]
Contact Width	1 mm[.039 in]
Contact Working Range (Low)	1 mm[.039 in]



Contact Working Range (High)	1.6 mm[.063 in]
Point of Contact Area Plating Material	Gold
Contact Current Rating (Max)	.5 A

Dimensions

Uncompressed Height	1.8 mm[.071 in]
---------------------	-----------------

Usage Conditions

Operating Temperature Range	-40 – 85 °C[-40 – 185 °F][-40 – 185 °F]
-----------------------------	---

Operation/Application

Circuit Application	Signal
---------------------	--------

Packaging Features

Packaging Quantity	6000
Packaging Method	Tape & Reel

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JAN 2021 (211) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Reflow solder capable to 260°C

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>



Compatible Parts



TE Part # 1674954-1


SHIELD FINGER 2026 WITH TAPE



TE Part # 1871059-1


SHIELD FINGER 1715 ON TAPE (EM

Customers Also Bought



TE Part #9-188275-0

FEMALE-ON-BOARD CONNECTOR
TOP ENTRY



TE Part #1367500-1

XFP Heat Sink



TE Part #1623916-3

3203X 10K



TE Part #1393194-7

T77S1D10-05



TE Part #1734193-1

WTB Socket,Terminal 80u" Tin



TE Part #1551631-5

1Shield Finger, Loose Piece



TE Part #1554901-1

SHIELD FINGER 2011 EMBOSS
PACKING



TE Part #1-1879061-5

CPF 0402 33R 0.1% 25PPM 5K RL



TE Part #103906-4

05 MTE HDR SRRA LATCH .100CL



TE Part #1061015-1

5863 0000 10,OSX PCB PLUG

Documents

Product Drawings

CAD Files

3D PDF

3D

Customer View Model



[ENG_CVM_CVM_1857724-4_G.2d_dxf.zip](#)

English

Customer View Model

[ENG_CVM_CVM_1857724-4_G.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_1857724-4_G.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

Products for Mobile Equipment

English

Spring Fingers Quick Reference Guide

English

Product Specifications

Product Specification

English

Product Environmental Compliance

TE Material Declaration

English