

TE Internal #: ZPF000000000001953
Connector Contacts, Pin, Operating Voltage 115 VAC, Operating Voltage 115 VDC, With Contact Retention Within Housing, Contact Size Code 20

[View on TE.com >](#)



Connectors > Rectangular Connectors > Connector Contacts



Contact Type: **Pin**
Operating Voltage: **115 VDC**
Contact Retention Within Housing: **With**
Contact Retention Type Within Housing: **Spring**

Features

Product Type Features

Barrel Type	Crimp
Connector System	Cable-to-Cable
Sealable	Yes
Connector & Contact Terminates To	Wire & Cable

Configuration Features

Compatible With Wire & Cable Type	Discrete Wire
-----------------------------------	---------------

Electrical Characteristics

Operating Voltage	115 VDC
-------------------	---------

Contact Features

Contact Type	Pin
Contact Retention Within Housing	With
Contact Size Code	20
Contact Base Material	Alumel
Contact Current Rating (Max)	7.5 A

Termination Features

Termination Method to Wire & Cable	Crimp
------------------------------------	-------

Mechanical Attachment

Contact Retention Type Within Housing	Spring
---------------------------------------	--------



Dimensions

Wire Size	.205 – .518 mm ²
-----------	-----------------------------

Usage Conditions

Operating Temperature Range	-65 – 175 °C[-85 – 347 °F]
-----------------------------	----------------------------

Operation/Application

Circuit Application	Power, Signal & Data
---------------------	----------------------

Product Compliance


For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Out of Scope
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JAN 2021 (211) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not reviewed for solder process capability


Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulations, TE’s information on SVHC in articles for this part number is still based on the European Chemical Agency (ECHA) ‘Guidance on requirements for substances in articles’(Version: 2, April 2011), applying the 0.1% weight on weight concentration threshold at the finished product level. TE is aware of the European Court of Justice ruling of September 10th, 2015 also known as O5A (Once An Article Always An Article) stating that, in case of ‘complex object’, the threshold for a SVHC must be applied to both the product as a whole and simultaneously to each of the articles forming part of its composition. TE has evaluated this ruling based on the new ECHA “Guidance on requirements for substances in articles” (June 2017, version 4.0) and will be updating its statements accordingly.


Customers Also Bought



TE Part #205164-5
AMPLIMITE,ASY,PLUG,109,2



TE Part #205162-6
AMPLIMITE,ASY,PLUG,109,1



TE Part #398703-000
55PC0224-22-2/6CS2502



TE Part #YDTS26F13-04BEV001
Straight Plug: D38999, 13-04 Insert,
Electroless Nickel Plating



TE Part #YDTS26W17-08AAV001
D38999: Straight Plug, 17-08 Insert



TE Part #ZPF000000000203986
DMC-MD 26 E-T



TE Part #2180283001
55A0811-18-2



TE Part #2180273001
55A0811-18-0



TE Part #YDIV46E23-55PDC003
PLUG ASSY



TE Part #D67481-000
NT-MIL-3/4-0-BULK-SP

Documents

Datasheets & Catalog Pages
DEUTSCH Contacts Quick Reference Guide
English