1604089-2 ✔ ACTIVE


AMP | AMP CPC

TE Internal #: 1604089-2

AMP CPC, Circular Connector Caps & Covers, Dust Cap, Compatible With Circular Connector Shell Size 11, Push/Pull

View on TE.com >

Connectors > Circular Connectors > Circular Connector Accessories > Circular Connector Caps & Covers > MINI CPC ACCESSORIES



Protection & Strain Relief Accessory Type: **Dust Cap**

Compatible With Circular Connector Shell Size: **11**

Cap to Flange Attachment: **Push/Pull**

Operating Temperature Range: **-55 – 105 °C [-67 – 221 °F]**

All MINI CPC ACCESSORIES (2)

Features

Product Type Features

Product Type	Accessory
Protection & Strain Relief Accessory Type	Dust Cap

Body Features

Sealing Cap Material	Thermoplastic
Color	Black
Cap Material	Elastomer

Mechanical Attachment

Cap to Flange Attachment	Push/Pull

Usage Conditions

Operating Temperature Range	-55 – 105 °C[-67 – 221 °F]

Operation/Application

For Use With	Receptacle
Compatible With Circular Connector Shell Size	11

Packaging Features

Packaging Quantity	1000
Packaging Method	Bag

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JAN 2021 (211) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not reviewed for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: https://echa.europa.eu/guidance-documents/guidance-on-reach

Compatible Parts



TE Part # CAT-AM71-C83998EE
MINI CPC


Also in the Series | AMP CPC



Circular Connector Adapters(7)



Circular Connector Boots & Strain Relief(6)



Circular Connector Caps & Covers(16)



Circular Connector Hardware(3)



Circular Connector Keying Plugs(2)




Circular Connector Seals(36)




Circular Power Connectors(513)



Insertion & Extraction Tools(1)



Power Contacts(5)



Sealing Sleeves(2)



Unscreened Circular Connector Backshells & Clamps(56)

Customers Also Bought




TE Part #1-1546406-1
ETHERNET CLOSURE CAP RECPT W /LANYRD



TE Part #1-770987-0
MINI UMNL PIN 22-18 AWG AU LP



TE Part #1-770988-0
MINI UMNL SOK 22-18AWG AU



TE Part #1-640517-0
02P MR II PLUG HSG



TE Part #1445420-2
SEAL,FLANGE,SIZE 11



TE Part #1445819-3
MINI CPC



TE Part #F939493001
55A0811-16-0(NS)

Documents

Product Drawings

CAP,DUST,SIZE 11

English

CAD Files

Customer View Model

ENG_CVM_1604089-2_A.3d_igs.zip

English

Customer View Model

ENG_CVM_1604089-2_A.3d_stp.zip

English

Customer View Model

ENG_CVM_1604089-2_A.2d_dxf.zip

English

3D PDF

English

By downloading the CAD file I accept and agree to the Terms and Conditions of use.

Datasheets & Catalog Pages

1-1773902-9_CPC_Catalog

German

1-1773902-9_CPC_Catalog

English

AMP Circular Connectors for Commercial Signal & Power Applications Continued

English

1-1773902-9_CPC_Catalog

Japanese

1-1773902-9_CPC_Catalog

Product Specifications

Application Specification

English