



Connectors > Circular Connectors > Standard Circular Connectors



Sealable: **No**
Hermetically Sealed: **No**
Contacts Preloaded: **No**
Shielded: **No**
Mating Retention: **Without**

Features

Product Type Features

Product Type	Accessory
Accessory Color	Black
Sealable	No

Configuration Features

Contacts Preloaded	No
--------------------	----

Body Features

Environmental Protection	Without
Hermetically Sealed	No

Mechanical Attachment

Mating Alignment	Without
Mating Retention	Without

Operation/Application

Shielded	No
----------	----

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold



EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JAN 2021 (211) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not reviewed for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 293708-1
NECTOR M SCREW NUT 5,6,7P



TE Part # 1-293708-1
NECTOR M SCREW NUT 5,6,7P

Also in the Series | NECTOR M Series



Circular Connector Hardware(1)




Plug & Socket Lighting Connector Accessories(1)



Rectangular Connector Hardware(13)



Rectangular Power Connectors(3)



Customers Also Bought

TE Part #2-1879444-8
Wirewound Resistor: Mineral, 2.5 Kw

TE Part #1-2176323-5
SMV 2W 1M5 5%

TE Part #6-2176245-9
CRGS1206 5% 470K

TE Part #5-2232356-3
POWER TRIPLE LOCK: Glow Wire Cap

TE Part #5-2232357-3
POWER TRIPLE LOCK GLOW WIRE PLUG

TE Part #1-293606-1
NECTOR M SKT HSG PANEL MOUNT

TE Part #2-6609037-7
12EP3=F8218

TE Part #CG3879-000
CI-7SHT201

TE Part #1-293607-1
NECTOR M CABLE NUT DIA 7.5-8.4 MM

TE Part #293596-1
NECTOR M SKT CAP

Documents

Product Drawings
NECTOR M SCREW NUT 3P
English

CAD Files
3D PDF
3D
Customer View Model
ENG_CVM_CVM_1-293481-1_B_c-1-293481-1-b.2d_dxf.zip



English

Customer View Model

[ENG_CVM_CVM_1-293481-1_B_c-1-293481-1-b.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_1-293481-1_B_c-1-293481-1-b.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Agency Approvals

[Agency Approval Document](#)

English