




Connectors > Terminal Blocks & Strips > Barrier Strips



Number of Positions: 3

Centerline (Pitch): 9.53 mm [.375 in]

Number of Rows: 1

Circuit Application: Power

Features

Product Type Features

Product Type	Barrier Strip
--------------	---------------

Configuration Features

Number of Positions	3
Number of Rows	1

Housing Features

Centerline (Pitch)	9.53 mm [.375 in]
--------------------	-------------------

Dimensions

Length	47.62 mm [1.875 in]
--------	---------------------

Operation/Application

Circuit Application	Power
---------------------	-------

Packaging Features

Packaging Method	Package
Packaging Quantity	50

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	

Current ECHA Candidate List: JAN 2021
(211)

Candidate List Declared Against: JUN 2015
(163)

SVHC > Threshold:
Not Yet Reviewed

Halogen Content

Not Yet Reviewed for halogen content

Solder Process Capability

Wave solder capable to 265°C


Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulations, TE's information on SVHC in articles for this part number is still based on the European Chemical Agency (ECHA) 'Guidance on requirements for substances in articles' (Version: 2, April 2011), applying the 0.1% weight on weight concentration threshold at the finished product level. TE is aware of the European Court of Justice ruling of September 10th, 2015 also known as O5A (Once An Article Always An Article) stating that, in case of 'complex object', the threshold for a SVHC must be applied to both the product as a whole and simultaneously to each of the articles forming part of its composition. TE has evaluated this ruling based on the new ECHA "Guidance on requirements for substances in articles" (June 2017, version 4.0) and will be updating its statements accordingly.

Compatible Parts



Customers Also Bought





TE Part #3-5102935-6
LEVEL V ASSY DR .125CL, 40, LE



TE Part #7-1879694-5
H8 6K81 0.1% 100PPM



TE Part #2-6609987-9
CORCOM SRB SERIES IEC FILTERED
INLETS



TE Part #202512-1
COR. GUIDE SOCKET ASSY.



TE Part #104892-5
50 50/50 GRID CBLE RECP W/LTCH



TE Part #205420-1
RECEPT ASSY,50 POSN,AMPLIMITE

Documents

Product Drawings

[6C1N03=SSB 3/8 SAFETY CVR 3CKT](#)

English

Datasheets & Catalog Pages

[BUCHANAN TERMINAL BLOCKS CATALOG - BARRIER STRIPS](#)

English