



Connectors > Circular Connectors > Standard Circular Connectors



Number of Positions: 19

Shell Plating Material: Sulfur Nickel Over Nickel

Shell Base Material: Brass

Circular Connector Insulation Material Type: LCP (Liquid Crystal Polymer)

Circular Connector Shell Size: M14

Features

Product Type Features

Product Type	Connector
Circular Connector Type	Plug
Shell Type	Metal

Configuration Features

Keying	A
Number of Positions	19
Contacts Preloaded	Yes

Body Features

Environmental Protection Type	Sealed
Environmental Protection	With
Shell Plating Material	Sulfur Nickel Over Nickel
Shell Base Material	Brass
Circular Connector Insulation Material Type	LCP (Liquid Crystal Polymer)

Contact Features

Contact Layout Arrangement	Circular
Circular Connector Contact Type	Pin

Mechanical Attachment

Mating Retention Type	Threaded Coupling
-----------------------	-------------------



Mating Alignment	With
Mating Alignment Type	Keyed
Mating Retention	With

Housing Features

Circular Connector Shell Size	M14
Alignment Keyed	215°

Usage Conditions

Operating Temperature Range	-50 – 150 °C
-----------------------------	--------------

Packaging Features

Packaging Quantity	20
--------------------	----

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Not Compliant
EU ELV Directive 2000/53/EC	Compliant with Exemptions
China RoHS 2 Directive MIIT Order No 32, 2016	Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JUL 2017 (174) SVHC > Threshold: Not Yet Reviewed
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Hand solderable with tin/lead solder

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>



Compatible Parts



TE Part # 2174214-3
Bayonet 19P Rece PS S-Cup Cont KIT /B



TE Part # 2174217-3
Bayonet 19P Rece PS S-Tail Cont KIT/B



TE Part # 2174217-1
Bayonet 19P Rece PS S-Tail Cont KIT/N

Customers Also Bought




TE Part #322366
DG 22-16COM22-18MIL HR R 10




TE Part #YDTS26W19-35SCC001
D38999: Straight Plug, 19-35 Insert



TE Part #2174217-2
Bayonet 19P Rece PS S-Tail Cont KIT/A



TE Part #1877700-1
Insert Asy,Socket, GPRBE3Q3SB




TE Part #127491-000
55PC1211-20-9-9CS2502



TE Part #165737-000
55PC2221-22-2/6-9CS2502



TE Part #202473-000
D-621-0438



TE Part #274869-000
SO63-1-9036-20



TE Part #1-1617033-0
HFW1206K03 = HFW 1/2 SIZE RELA



TE Part #340037-000
55PC1124-24-2/6-9CS2502

Documents

Product Drawings
Bayonet 19P Plug PS S-Cup Cont KIT/A
English

CAD Files
3D PDF
3D



Customer View Model

[ENG_CVM_CVM_2174211-2_D.2d_dxf.zip](#)

English

Customer View Model

[ENG_CVM_CVM_2174211-2_D.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_2174211-2_D.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

[Metal-Shell Micro Circular Connectors](#)

English

Product Specifications

[Application Specification](#)

Japanese