




Terminals & Splices > Terminal Housings, Insulation Sleeves & Blocks > Crimp Terminal Housings



Terminal & Splice Type: **Tab**
Housing Type: **Tab Housing**
Number of Crimp Terminal Housing Positions: **5**
Crimp Terminal Housing Terminal Orientation: **Straight**
Crimp Terminal Housing UL Flammability Rating: **UL 94V-2**

Features

Product Type Features

Product Type	Terminal Housing
Style Code	C
Housing Type	Tab Housing
Sealable	No
Insulated	No

Configuration Features

Number of Crimp Terminal Housing Positions	5
--	---

Body Features

Crimp Terminal Housing Housing Color	Natural
Crimp Terminal Housing Mating Retention	With
Crimp Terminal Housing Mating Alignment	With

Contact Features

Terminal & Splice Type	Tab
Crimp Terminal Housing Terminal Orientation	Straight



Mechanical Attachment

Mating Alignment Type	Polarization
Mating Retention Type	Locking Lance
Crimp Terminal Housing Mounting Style	Panel Mount

Housing Features

Crimp Terminal Housing Housing Material	Polyamide
---	-----------

Dimensions

Length	30.5 mm[1.2 in]
Crimp Terminal Housing Centerline	5 mm[.196 in]

Usage Conditions

Operating Temperature Range	-40 – 105 °C[-40 – 221 °F]
-----------------------------	----------------------------

Industry Standards

Crimp Terminal Housing UL Flammability Rating	UL 94V-2
---	----------

Packaging Features

Packaging Quantity	200
--------------------	-----

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JAN 2021 (211) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability


Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these




limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>


Compatible Parts

 TE Part # 9-927742-3 FASTIN FASTON HOUSING 3POS	 TE Part # 9-927742-2 2POS FASTIN FASTON HOUSING	 TE Part # 1241967-8 FASTIN FASTON TAB HOUSING 8P	 TE Part # 964492-2 2 POS FASTIN/ON HOUSING PANEL MOUNT
 TE Part # 5-964492-5 FASTIN FASTON HOUSING 5POS	 TE Part # 928309-8 8P FF FLACHST GEH	 TE Part # 927742-6 6 POS FASTIN/ON HOUSING PANEL MOUNT	 TE Part # 293011-1 5 POS. FASTIN-FASTON CONN. TAB HOUSING R
 TE Part # 9-927742-4 4POS FASTIN FASTON HOUSING	 TE Part # 927742-2 2 POS FASTIN/ON HOUSING PANEL MOUNT	 TE Part # 7-927742-6 6 POS. FASTIN-FASTON* TAB HSG RAST5	 TE Part # 293009-1 4 POS. FASTIN-FASTON CONN. TAB HOUSING R
 TE Part # 284985-1 7 POS. FASTIN-FASTON CONN. TAB HSG, RAST	 TE Part # 1955416-1 3 POS. FASTIN-FASTON CONNECTOR TAB HOUSING	 TE Part # 284986-1 8 POS. FASTIN-FASTON CONN. TAB HSG, RAST	 TE Part # 927742-4 4 POS FASTIN/ON HOUSING PANEL MOUNT






TE Part # 1-1241968-5
FASTIN FASTON HOUSING 10P



TE Part # 1-927742-6
6 POS. FASTIN-FASTON* TAB HSG RAST5




TE Part # 1241969-8
FASTIN FASTON HOUSING 8P



TE Part # 2-927742-3
3P FF FLACHSTGH6,3

Also in the Series | RAST 5 IDC Connectors



Automotive Terminals(8)



Connector Contacts(12)




Crimp Terminal Housings(41)



Insertion & Extraction Tools(1)



Rectangular Connector Housings(1)



Standard Edge Connectors(36)



Standard Rectangular Connectors(138)



Wire-to-Board Connector Assemblies & Housings(214)



Wire-to-Board Connector Contacts(2)




Wire-to-Board Headers & Receptacles (424)


Customers Also Bought



TE Part #1742198-1
250 FASTON,REC.,18-14 AWG,NPST



TE Part #1747050-1
Glow Wire GRACE INERTIA Plug



TE Part #1-88859-3
2.54mm FFC Connectors Receptacle Housing




TE Part #1241961-1
STD TIM HOUSING MKII 2POS





TE Part #1217689-1
SPECIAL LEAF CONTACT,300 SERIE



TE Part #1955416-1
3 POS. FASTIN-FASTON
CONNECTOR TAB HOUSI



TE Part #969116-2
AMPLIVAR SOCKET 6,3 SPECIAL



TE Part #1743067-2
TERMINAL BLOCK FOR DRYER

TE Part #2318950-1
NEW GIC 3.3 REC CONTACT TIN
PLATE



TE Part #1742492-1
BRUSH CONT TABLOCK FLAG LH 14-
20AWG PBR

Documents

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_1241857-5_D.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_1241857-5_D.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_1241857-5_D.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

FASTIN_FASTON_Product_Line

English

Product Environmental Compliance

MD_1241857-5_110320152148_dmtec

English

MD_1241857-5_110320152148_dmtec

English

Agency Approvals

UL Report

English

1241857-5

RAST 5 IDC Connectors, Crimp Terminal Housings, Tab, Tab Housing, 5 Position,
Straight, UL 94V-2, Natural Crimp Terminal Housing Housing Color

