




Terminals & Splices > Ring Terminals & Spade Terminals



Wire Size: .5 – 1 mm²

Ring & Spade Barrel Type: **Closed Barrel**

Ring & Spade Terminal Orientation: **Straight**

Ring & Spade Overall Length: **30 mm [1.18 in]**

Features

Product Type Features

Ring & Spade Barrel Type	Closed Barrel
Sealable	Yes
Insulated	Yes
Ring & Spade Wire/Cable Type	Regular Wire
Support Style	Insulation Support

Configuration Features

Terminal Angle	Straight
----------------	----------

Body Features

Inspection Slot	No
Insulation Sleeve Color	Red
Weight per Piece	1 g
Ring & Spade Plating Material	Tin

Contact Features

Ring & Spade Terminal Orientation	Straight
-----------------------------------	----------

Mechanical Attachment

Wire Insulation Support	With
-------------------------	------

Dimensions

Wire Size	.5 – 1 mm²
-----------	------------



Ring & Spade Overall Length	30 mm[1.18 in]
-----------------------------	----------------

Usage Conditions

Insulation Requirement	Fully Insulated
Operating Temperature Range	-55 – 125 °C

Operation/Application

Heavy Duty	No
------------	----

Industry Standards

Government Qualified	No
----------------------	----

Packaging Features

Packaging Quantity	100
Ring & Spade Packaging Method	Box

Other

Comment	Crimp Termination
---------	-------------------

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JAN 2021 (211) Does not contain REACH SVHC
Halogen Content	BFR/CFR/PVC Free, but Br/Cl >900 ppm in other sources.
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides



on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

TE Part # CJ2087-000
HL2010E-KIT-120V

Customers Also Bought

TE Part #2-1879460-5
Thick Film Resistor: Current Sense

TE Part #150699-2
187 FASTON,FLAG,REC.,20-16 AWG, TPBR

TE Part #HD10-9-1939PE
DEUTSCH HD10 HOUSINGS

TE Part #1-967626-6
TIMER, CONNECTOR HOUSING

TE Part #170020-2
SHUR PLUG 20-14 MM2 TPBR

TE Part #170021-2
SHUR PLUG RECEPTACLE 20-16 AWG TPBR

TE Part #182485-4
FF 187 REC 0.5-1.5MM2 TPPB LP

TE Part #1-1633919-6
ANVIL COMBINATION

TE Part #1418885-3
AMP MCP 1.5K, CONTACT, SWS, (LP)

Documents

Product Drawings

B-106-8401

English



Datasheets & Catalog Pages

1654025_Sec8_B-106

English

Raychem Electrical Interconnect Products

English

Product Specifications

Installation Procedure for Duraseal Splices and Terminals

English