



TE Internal #: 1-1437720-3

Standard Circular Connectors, Wire-to-Panel, 3 Position, Sealable, Printed Circuit Board, 3A Contact Current Rating (Max), Signal, Board Mount

[View on TE.com >](#)

Connectors > Circular Connectors > Standard Circular Connectors



Connector System: **Wire-to-Panel**

Number of Positions: **3**

Sealable: **Yes**

Connector & Contact Terminates To: **Printed Circuit Board**

Contact Current Rating (Max): **3 A**

Features

Product Type Features

Product Type	Connector
Connector System	Wire-to-Panel
Sealable	Yes
Connector & Contact Terminates To	Printed Circuit Board
Circular Connector Type	Receptacle
Shell Type	Metal

Configuration Features

Number of Positions	3
Number of Power Positions	0
Number of Signal Positions	3
Contacts Preloaded	Yes

Body Features

Shell Plating Material	Nickel
Shell Base Material	Zinc Die Cast
Circular Connector Insulation Material Type	Polyamide

Contact Features

Contact Current Rating (Max)	3 A
Reverse Gender	Yes
Contact Layout Arrangement	Circular



Circular Connector Contact Type	Socket
---------------------------------	--------

Mechanical Attachment

Connector Mounting Type	Board Mount
Mating Alignment Type	Keyed
Mating Retention	With

Usage Conditions

Operating Temperature Range	-40 – 80 °C[-40 – 176 °F]
-----------------------------	---------------------------

Operation/Application

Circuit Application	Signal
Shielded	Yes

Product Compliance

For compliance documentation, visit the product page on TE.com>


EU RoHS Directive 2011/65/EU	Not Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JAN 2021 (211) SVHC > Threshold: Pb (4% in Component Part) <b>Article Safe Usage Statements:</b> Do not eat, drink or smoke when using this product. Wash thoroughly after handling. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location.
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Hand solderable with lead free solder

Product Compliance Disclaimer


This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>



### Compatible Parts




TE Part # 1-1437720-7  
T01-0598-PP03-A=SHIELDED SUBMI




TE Part # 2-1437720-3  
T01-0599-B03-B=INDUSTRIAL CONN


### Customers Also Bought




TE Part #216165-1  
D-Sub Crimp Recpt Signal 26 Posn,  
Socket Size 22, Shell Size 2




TE Part #1-179228-0  
AMP COMMON TERMINATION  
HOUSINGS




TE Part #216164-1  
15P.HDP22 REC.ASSY.




TE Part #1-1437719-2  
T01-0540-P05-MALE PLUG  
CONNECTOR-CRIMP




TE Part #1658526-4  
609-1030LF FEM SOCKT,LEAD FREE




TE Part #1-1658526-8  
609-3430LF FEM SOCKT,LEAD FREE




TE Part #1-1437719-3  
T01-0540-S03-FEMALE PLUG  
CONNECTOR-CRIMP



TE Part #GA100K6A1A  
DISCRETE NTC SERIES I



TE Part #1-1437720-4  
T01-0590-PS05



TE Part #1230032-1  
FEMALE SCREWLOCK M3

### Documents

Product Drawings

T01-0590-PS03=T01-0590-PS03

English

Product Specifications

Application Specification



English