



EMI Filters > IEC Unfiltered Inlets > CORCOM CU SERIES IEC UNFILTERED INLETS



Filter Current Rating: 15 A

Input Connector Type: IEC 60320/C-14

Input Connector Style: Male Receptacle

Filter Output Termination Type: 3/16" Faston

Voltage Rating (Max): 250 VAC

All CORCOM CU SERIES IEC UNFILTERED INLETS (4)

Features

Product Type Features

Input Connector Type	IEC 60320/C-14
Input Connector Style	Male Receptacle
Filter Output Termination Type	3/16" Faston

Electrical Characteristics

Filter Current Rating	15 A
Voltage Rating (Max)	250 VAC

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Not Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JAN 2021 (211) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free



Solder Process Capability

Not applicable for solder process capability


Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # CAT-C8114-C8911
CORCOM CU SERIES MULTI-FUNCTION INLET FI



TE Part # 1609142-1
GA400 POWER LINE CO=F6946

Also in the Series | Corcom CU




IEC Unfiltered Inlets(4)



Multi-Function Inlet Filters(19)


Customers Also Bought



TE Part #1-338084-3
RJ22 Connectors




TE Part #1-1609112-5
CORCOM CU SERIES MULTI-FUNCTION INLET FI



TE Part #1-2176232-7
SMD Power Resistor: 3 Watt, 1% Tol



TE Part #1-1423673-1
W51-A122B1-8=CKTBKR,THERM, ROCK



Documents

Product Drawings

15CU15S1=F8314

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_1-1609112-8_B.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_1-1609112-8_B.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_1-1609112-8_B.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

1654001_CORCOM_PRODUCT_GUIDE

English

1654001_Corcom_Product_Guide_CU_Series

English

1-1654250-1_CORCOM_EMI_RFI_QRG

English

CORCOM_CU_SERIES

English



Corcom Combined Selector Charts

English

Agency Approvals

APPLIANCE INLET, CU SERIES, CB TEST CERTIFICATE

English