




Terminals & Splices > Ring Terminals & Spade Terminals



Terminal & Splice Type: **Ring Tongue**
Wire Size: **13100 – 20800 CMA**
Ring & Spade Stud Size: **1/4**

Features

Product Type Features

Ring & Spade Stud Size	1/4
Ring & Spade Barrel Type	Closed Barrel
Sealable	No
Insulated	Yes
Ring & Spade Wire/Cable Type	Regular Wire
Support Style	Non - Insulation Support

Configuration Features

Terminal Angle	Straight
----------------	----------

Body Features

Ring & Spade Plating Material	Nickel
-------------------------------	--------

Contact Features

Terminal & Splice Type	Ring Tongue
Ring & Spade Terminal Orientation	Straight

Mechanical Attachment

Wire Insulation Support	With
-------------------------	------

Dimensions

Wire Size	13100 – 20800 CMA
Stud Diameter	5 mm[.197 in]
Tongue Thickness	.79 mm[.031 in]



Ring & Spade Overall Length	38 mm[1.5 in]
Barrel Inside Diameter	4.37 mm[.172 in]

Usage Conditions

Insulation Requirement	Partially Insulated
Operating Temperature Range	288 °C[550 °F]

Operation/Application

Heavy Duty	No
------------	----

Industry Standards

Government Qualified	No
----------------------	----

Packaging Features

Packaging Quantity	25
Ring & Spade Packaging Method	Box & Carton

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JAN 2021 (211) Does not contain REACH SVHC
Halogen Content	Low Bromine/Chlorine - Br and Cl < 900 ppm per homogenous material. Also BFR /CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>



Compatible Parts



TE Part # 69216
HYP8/10 SOLIS 8AWG DIE SET




TE Part # 69211-1
HYP8/10 STRATO-THERM 8AWG DIE SET


Customers Also Bought



TE Part #1577630-1
TERMINAL RT PIDG PEEK STRATO 18-16 AWG




TE Part #1577621-1
TERMINAL RT PIDG PEEK STRATO 24-22 AWG



TE Part #1577622-1
TERMINAL, PEEK PIDG STRATO, 20AWG




TE Part #153927-000
HEX40-AC-90-13-A3-1



TE Part #2-160759-1
POSITIVE LOCK 250 REC 0.5-1.5MM2 NPPHBRZ



TE Part #1577633-1
TERMINAL RT PIDG PEEK STRATO 18-16 AWG




TE Part #132331-1
TERMINAL STRATO-THERM POST INS



TE Part #132391-1
COAXICON RF ANGLE PLUG C



TE Part #1918933-4
Std Cbl Adp w Boot, HA 5.5



TE Part #ZPF000000000020170
FMJ 12E 22-02

Documents

Product Drawings
TERMINAL, STRATO, POST INS, 8
English

Product Environmental Compliance
TE Material Declaration



English