1-1888021-2 ✔ ACTIVE


Mini-SAS

TE Internal #: 1-1888021-2

Mini-SAS, Mini-SAS, Through Hole - Solder, Shell, Printed Circuit Board, .5A Contact Current Rating (Max), Board Mount

View on TE.com >

Connectors > PCB Connectors > SAS & MiniSAS > Mini-SAS Shielded Receptacle:Right Angle




SAS Connector Type: **Mini-SAS**

Termination Method to Printed Circuit Board: **Through Hole - Solder**

SAS Connector Accessory Type: **Shell**

Connector & Contact Terminates To: **Printed Circuit Board**

Contact Current Rating (Max): **.5 A**

All Mini-SAS Shielded Receptacle:Right Angle (2)

Features

Product Type Features

SAS Connector Type	Mini-SAS
SAS Connector Accessory Type	Shell
Connector & Contact Terminates To	Printed Circuit Board

Configuration Features

Key Type	2
Stackable	No

Contact Features

Contact Current Rating (Max)	.5 A

Termination Features

Termination Post & Tail Length	2.8 mm[.11 in]
Termination Method to Printed Circuit Board	Through Hole - Solder

Mechanical Attachment

PCB Mount Retention	Without

Connector Mounting Type	Board Mount

Usage Conditions

Operating Temperature Range	-55 – 105 °C[-67 – 221 °F]

Packaging Features

Packaging Quantity	150
Packaging Method	Box & Tray, Package

Product Compliance


For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JAN 2021 (211) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: https://echa.europa.eu/guidance-documents/guidance-on-reach

Compatible Parts



TE Part # CAT-M6907-C76264
Mini-SAS Shielded Receptacle Assemblies

Also in the Series | Mini-SAS



SAS & MiniSAS(29)


Customers Also Bought




TE Part #1-1932000-0
DDR3 DIMM SOCKETS



TE Part #1-6609000-3
CORCOM EEA SERIES IEC FILTERED INLETS



TE Part #1888019-6
Mini-SAS Shielded Receptacle Assemblies




TE Part #100526-3
Z-PACK F.CODING KEY



TE Part #1888251-1
Low Profile,RJ45,1x4,GRN/YEL



TE Part #7-1393132-0
P40P42A12P1-120=CONTACTORS



TE Part #103168-4
12 MODII HDR DRST SHRD .100CL



TE Part #1565691-1
DDR2 SO DIMM Sockets

Documents

Product Drawings

shield recpt ra 36pos press fit sff

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_1-1888021-2_A.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_1-1888021-2_A.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_1-1888021-2_A.3d_stp.zip

English

By downloading the CAD file I accept and agree to the Terms and Conditions of use.

Datasheets & Catalog Pages

EVERCLEAR Mini Multi-Lane High Speed Interconnects Datasheet 1773447-2

English

Product Specifications

Product Specification

English