




Terminals & Splices > Quick Disconnects



Terminal & Splice Type: **Receptacle**

Wire Size: **.25 – .34 mm²**

Quick Disconnect Mating Tab Width: **2.8 mm [.11 in]**

Quick Disconnect Mating Tab Thickness: **.51 mm [.02 in]**

Features

Product Type Features

Wire Stop	No
Wire/Cable Type	Regular Wire
Terminates To	Wire & Cable
Sealable	No
Insulated	No

Configuration Features

Connection Capacity	Single
---------------------	--------

Body Features

Fully Insulated	No
Quick Disconnect Plating Material	Pre-Tin

Contact Features

Terminal Type	Receptacle
Terminal & Splice Type	Receptacle
Quick Disconnect Terminal Orientation	Straight



Contact Base Material	Brass
Crimp Type	F-Crimp
Barrel Type	Open

Mechanical Attachment

Mating Retention Type	Dimple
Wire Insulation Support	With

Dimensions

Accepts Wire Insulation Diameter Range	1.02 – 1.52 mm[.04 – .06 in]
Overall Length	16 mm[.63 in]
Receptacle Terminal Stock Thickness	.08 mm[.003 in]
Wire Size	.25 – .34 mm ²
Quick Disconnect Mating Tab Width	2.8 mm[.11 in]
Quick Disconnect Mating Tab Thickness	.51 mm[.02 in]

Usage Conditions

Insulation Requirement	Uninsulated
Operating Temperature Range	-40 – 110 °C[-40 – 230 °F]

Industry Standards

UL Rating	Listed
CSA Certified	Yes

Packaging Features

Packaging Quantity	10000
Quick Disconnect Packaging Method	Strip/Reel

Other

Line	Premier
------	---------

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211)



Candidate List Declared Against: JAN 2021 (211)
Does not contain REACH SVHC

Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

TE Part # 2-2150546-1
OC-PA-E-FM-062F070O-001-0034

TE Part # 2-2150546-2
OC-PA-E-FA-062F070O-001-0034

TE Part # 2150546-1
OC-AT-E-FM-062F070O-001-0034

TE Part # 2150546-2
OC-AT-E-FA-062F070O-001-0034

KIT
REPRESENTATION ONLY
TE Part # 7-2150546-7
OC-062F070O-CRIMPTOOLINGKIT

Also in the Series | **FASTON 110**



Crimp Terminal Housings(17)



Insertion & Extraction Tools(1)



PCB Terminals(22)




Quick Disconnects(182)

Customers Also Bought




TE Part #926893-3
UNIV.M-N-L.SOCKET




TE Part #1-215307-6
2X16P HV100 REC CON. TE, 7.0MM



TE Part #160163-2
RING TONGUE WITH IS 3.1-5.3 MM2
TPBR



TE Part #1-215307-2
2X12P HV100 REC CON. TE, 7.0MM




TE Part #146839-4
50 MC HDR VERT SMTW/BRD LOC



TE Part #160101-9
RING TONGUE 20-16 AWG 0.0253
NPBR




TE Part #160366-2
FF 110 SR. REC 22-20AWG TPBR



TE Part #1546216-2
TERMI-BLOK PCB MOUNT 90 2P.



TE Part #1-1803095-3
FLOATING SHEAR, FRONT



TE Part #1333208-2
ANVIL, COMBINATION (.120)

Documents

Product Drawings

110 FASTON,REC.,24-22 AWG,PTBR

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_140716-2_Z.2d_dxf.zip



English

Customer View Model

[ENG_CVM_CVM_140716-2_Z.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_140716-2_Z.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

[Application Specification](#)

English

Agency Approvals

[Agency Approval Document](#)

English