
1445995-1 ✔ ACTIVE

TE Internal #: 1445995-1

Power Contacts, Contact, Operating Voltage 600 VAC, Operating Voltage 600 VDC, Silver, 2AWG Wire Size, 34 – 35mm² Wire Size

View on TE.com >

Connectors > Power Connectors > Power Contacts







Power Contact Type: **Contact**

Operating Voltage: **600 VDC**

Contact Mating Area Plating Material: **Silver**

Wire Size: **2 AWG**

Features

Product Type Features

Power Contact Type	Contact
Connector System	Wire-to-Wire
Connector & Contact Terminates To	Wire & Cable

Electrical Characteristics

Operating Voltage	600 VDC

Contact Features

Contact Mating Area Plating Material	Silver
Contact Current Rating (Max)	120 A
Contact Type	Tab
Contact Retention Within Housing	With
Mating Tab Width	10.6 mm[.417 in]
Mating Tab Thickness	4.85 mm[.191 in]
Contact Base Material	Copper Alloy
Contact Mating Area Plating Material Thickness	1.27 µm[50 µin]
Wire Contact Termination Area Plating Material Thickness	50 µm[1.27 µin]
Wire Contact Termination Area Plating Material	Silver

Wire Contact Termination Area Plating Material Finish	Matte
Contact Orientation	Straight
Contact Underplating Material	Nickel
Contact Underplating Material Thickness	50 µm[1.27 µin]
Barrel Type	Closed Barrel

Termination Features

Termination Method to Wire & Cable	Crimp

Mechanical Attachment

Connector Mounting Type	Cable Mount (Free-Hanging)

Dimensions

Wire Size	67100 – 69073 CMA

Usage Conditions

Operating Temperature Range	-40 – 105 °C[-40 – 221 °F]

Operation/Application

Circuit Application	Power

Industry Standards

Agency/Standard	UL
UL Rating	Recognized
UL Flammability Rating	UL 94V-0
UL File Number	E28476

Packaging Features

Packaging Method	Loose Piece
Packaging Quantity	1

Other

Wire/Cable Type	Discrete Wire
Wire Type	Stranded

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold

EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JUN 2020 (209) SVHC > Threshold: Not Yet Reviewed
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: https://echa.europa.eu/guidance-documents/guidance-on-reach

Customers Also Bought



TE Part #1445957-5
HSG SUB ASY,RED



TE Part #1445957-1
HSG SUB ASY,BLUE



TE Part #1445957-2
HSG SUB ASY,BLACK




TE Part #1445957-3
HSG SUB ASY,WHITE




TE Part #1-1827872-4
DYNAMIC 1100 HDR ASSY




TE Part #HDP26-24-19SN-L017
DEUTSCH HDP20 HOUSINGS



TE Part #1-316132-2
DYNAMIC 3200 HDR ASSY



TE Part #1393310-4
VCF7-1000=FROM SEC



TE Part #1-1904045-2
V23333Z1001A008-EV-100



TE Part #1-2213767-7
AV19 SPM 5A MOVE RING LED BLUE 12V

Documents

Product Drawings

CONTACT, 120 PWR PROD,2AWG

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_1445995-1_A.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_1445995-1_A.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_1445995-1_A.3d_stp.zip

English

By downloading the CAD file I accept and agree to the Terms and Conditions of use.

Datasheets & Catalog Pages

POWER_CONNECTORS_CATALOG_SEC02_CABLE_MOUNTED

English

2_PIECE_POWER_CONNECTORS_qrg_4-1773458-1

English

Product Specifications

Application Specification

English

Product Environmental Compliance

TE Material Declaration

English

Agency Approvals

Agency Approval Document

English