



PIDG

TE Internal #: 151438
PIDG, Ring Terminals & Spade Terminals, Ring Tongue, 24 – 22AWG Wire Size, .2 – .3mm² Wire Size, 509 – 810CMA Wire Size, M2.5

[View on TE.com >](#)

Terminals & Splices > Ring Terminals & Spade Terminals



Terminal & Splice Type: **Ring Tongue**
Wire Size: **509 – 810 CMA**
Ring & Spade Stud Size: **M2.5**

Features

Product Type Features

Shape Description	RING-041
Ring & Spade Stud Size	M2.5
Ring & Spade Barrel Type	Closed Barrel
Sealable	No
Insulated	Yes
Ring & Spade Wire/Cable Type	Regular Wire
Support Style	Non - Insulation Support

Configuration Features

Number of Holes	1
Terminal Angle	Straight

Electrical Characteristics

Voltage (Max)	300 V
---------------	-------

Body Features

Insulation Sleeve Color	Black
Weight per Piece	.706 g
Stripe Color	Black
Ring & Spade Plating Material	Copper, Tin

Contact Features

Terminal & Splice Type	Ring Tongue
------------------------	-------------



Ring & Spade Terminal Orientation	Straight
-----------------------------------	----------

Mechanical Attachment

Wire Insulation Support	With
-------------------------	------

Dimensions

Wire Size	509 – 810 CMA
Stud Diameter	3 mm[.118 in]
Tongue Thickness	.79 mm[.031 in]
Ring & Spade Overall Length	19.98 mm[.79 in]
Ring & Spade Wire Insulation Diameter (Max)	2.54 mm[.1 in]
Ring & Spade Wire Insulation Diameter	.89 – 2.54 mm[.035 – .1 in]

Usage Conditions

Insulation Requirement	Partially Insulated
Operating Temperature Range	105 °C[221 °F]

Operation/Application

Heavy Duty	No
------------	----

Industry Standards

Government Qualified	No
----------------------	----

Packaging Features

Packaging Quantity	1000
Ring & Spade Packaging Method	Box

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JAN 2021 (211) Does not contain REACH SVHC
Halogen Content	Not Yet Reviewed for halogen content
Solder Process Capability	Not applicable for solder process capability



Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

TE Part # 576778
HHHT PIDG PEEK STRATO 24-22 ASSY

TE Part # 1901611-2
CCII PIDG STRATO 24-20 ASSY

TE Part # 1901611-1
CCII PIDG STRATO 24-20 ASSY

TE Part # 69692-1
T-HEAD PIDG STRATO 26-20 ASSY

Also in the Series | PIDG

Compression Connectors(17)

Crimp Terminal Housings(1)

Crimp Wire Pins, Tabs & Ferrules(41)

Knife Disconnects(11)

PCB Terminals(9)

Portable Crimp Tools(2)

Quick Disconnects(53)

Ring Terminals & Spade Terminals(862)



Special Purpose Terminals(1)



Splices(48)

Customers Also Bought



TE Part #1-51864-1
PIDG RING TONGUE TERMINALS



TE Part #151439
PIDG 22 RING #6



TE Part #131644-1
TERM, PIDG, 20 AWG, IR, #4 STUD



TE Part #131648-1
TERMINAL RING TONGUE PIDG 22 18




TE Part #152872
14-12 PIDG NYLON RT NO 10WHITE



TE Part #1393824-5
CRADLE RELAY ACCESSORY



TE Part #151440
PIDG 22 RING #8



TE Part #ZPF000000000112147
PRISE EQUILIBRAGE TYPE 700E - 6.488.000

Documents

Product Drawings

PIDG 22 RING #4

English

Datasheets & Catalog Pages

RADIATION_RESISTANT_PRE-INSULATED_TERMINALS_SPLICES

English

Product Specifications

Application Specification

English