
1544458-2 ✔ ACTIVE



TE Internal #: 1544458-2

Housing for Female Terminals, Wire-to-Wire, 2 Position, 10.9mm [.429in] Centerline, Gray, Wire & Cable, Power

View on TE.com >

Connectors > Automotive Connectors > Connector Housings



Connector & Housing Type: **Housing for Female Terminals**

Mating Tab Width: **8 mm [.315 in]**

Connector System: **Wire-to-Wire**

Number of Positions: **2**

Centerline (Pitch): **10.9 mm [.429 in]**

Features

Product Type Features

Connector & Housing Type	Housing for Female Terminals
Connector System	Wire-to-Wire
Sealable	No
Hybrid Connector	No
Primary Locking Feature	Integrated in Housing
Connector & Contact Terminates To	Wire & Cable

Configuration Features

Number of Positions	2
Number of Rows	1

Body Features

Cable Exit Angle	180°
Body Material	PA
Primary Product Color	Gray

Contact Features

Mating Tab Width	8 mm[.315 in]

Mechanical Attachment

Mounting Feature	Without
Terminal Position Assurance	No
Strain Relief	No
Mating Alignment Type	Polarized

Housing Features

Centerline (Pitch)	10.9 mm[.429 in]

Dimensions

Product Width	32.5 mm[1.27 in]
Product Length	22.6 mm[.889 in]
Product Height	11.8 mm[.464 in]

Operation/Application

Circuit Application	Power

Packaging Features

Packaging Quantity	1500
Packaging Method	Box

Other

Serviceable	No
Connector Position Assurance Capable	No

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JUN 2020 (209) SVHC > Threshold: Not Yet Reviewed
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: https://echa.europa.eu/guidance-documents/guidance-on-reach

Compatible Parts



TE Part # 1544455-1
CLIP8MM ECHANCRE S



TE Part # 1544142-1
CLIP8MM ECHANCRE S



TE Part # 1544128-1
CLIP 8 MM STOL SEC



TE Part # 1544141-1
CLIP8MM ECHANCRE S



TE Part # 1544129-1
CLIP 8 MM STOL SEC

Customers Also Bought



TE Part #1-965641-7
TIMER, CONNECTOR HOUSING



TE Part #1-962916-1
TIMER, RECEPTACLE AND TAB




TE Part #100866-2
ECONOSEAL, CONNECTOR HOUSING



TE Part #185402-1
MODULAR RELAY HOLDER



TE Part #1544458-1
BOITIER PC 8 MM 2



TE Part #CD20543001
ACW0219-1.00-93(NS)



TE Part #1393436-4
V23542C1028B300=KABELBAUMST. 8



TE Part #1544141-1
CLIP8MM ECHANCRE S

TE Part #1544458-3
BOITIER PC 8 MM 2

Documents

Product Drawings

BOITIER PC 8 MM 2

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_1544458-2_C.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_1544458-2_C.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_1544458-2_C.3d_stp.zip

English

By downloading the CAD file I accept and agree to the Terms and Conditions of use.