




Terminals & Splices > Ring Terminals & Spade Terminals



Terminal & Splice Type: **Ring Tongue**
Wire Size: **150500 – 190000 CMA**
Ring & Spade Stud Size: **3/8**

Features

Product Type Features

Ring & Spade Stud Size	3/8
Ring & Spade Barrel Type	Closed Barrel
Sealable	No
Insulated	No
Ring & Spade Wire/Cable Type	Stranded
Support Style	Non - Insulation Support

Configuration Features

Terminal Angle	Straight
----------------	----------

Body Features

Ring & Spade Plating Material	Nickel
-------------------------------	--------

Contact Features

Terminal & Splice Type	Ring Tongue
Ring & Spade Terminal Orientation	Straight

Mechanical Attachment

Wire Insulation Support	Without
-------------------------	---------

Dimensions

Wire Size	150500 – 190000 CMA
Stud Diameter	10.5 mm[.413 in]
Tongue Thickness	.79 mm[.031 in]



Ring & Spade Overall Length	53.65 mm[2.11 in]
Barrel Inside Diameter	14.35 mm[.565 in]

Usage Conditions

Insulation Requirement	Uninsulated
Operating Temperature Range	170 °C[338 °F]

Operation/Application

Heavy Duty	No
------------	----

Industry Standards

Government Qualified	No
----------------------	----

Packaging Features

Packaging Quantity	100
Ring & Spade Packaging Method	Box

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JAN 2021 (211) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>



Compatible Parts



TE Part # 134540-1
TERMINAL SOLISTRAND 16-14 BT-BT



TE Part # 133521-1
TERMINAL SOLISTRAND 22-18, GOLD PLATED

Customers Also Bought



TE Part #132104-2
TERMINAL RING TONGUE SOLISTRAN



TE Part #696192-000
B-006-04



TE Part #CW3225-000
B-013-15




TE Part #YDTS26W21-41SBV001
D38999: Straight Plug, 21-41 Insert



TE Part #ZPF00000000000000378
006-0973-20 A



TE Part #1740413-1
PIN, COAX , KIT, SIZE 8




TE Part #354499-000
DK-3716-F101-TP



TE Part #ZPF0000000000137694
DMC-M 99-10 AA



TE Part #5058602008
RNF-100-1-1/4-6-STK



TE Part #5-1879743-0
RP 1J 15R4 0.1% 15PPM CUT LENGTH

Documents

Product Drawings
TERMINAL SOLISTRAND 3/0
English

CAD Files
3D PDF



3D

Customer View Model

[ENG_CVM_CVM_135536-1_A.2d_dxf.zip](#)

English

Customer View Model

[ENG_CVM_CVM_135536-1_A.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_135536-1_A.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

[RADIATION_RESISTANT_PRE-INSULATED_TERMINALS_SPLICES](#)

English