




Terminals & Splices > Quick Disconnects



Terminal & Splice Type: **Tab**

Wire Size: **.82 – 2.08 mm²**

Quick Disconnect Mating Tab Width: **6.35 mm [.25 in]**

Quick Disconnect Mating Tab Thickness: **.81 mm [.032 in]**

Features

Product Type Features

Wire Stop	No
Wire/Cable Type	Regular Wire
Terminates To	Wire & Cable
Quick Disconnect Insertion Force	Normal
Sealable	No
Insulated	No

Configuration Features

Connection Capacity	Single
---------------------	--------

Electrical Characteristics

Voltage (Max)	250 V
---------------	-------

Body Features

Fully Insulated	No
Quick Disconnect Plating Material	Tin

Contact Features

--	--



Terminal Type	Tab
Terminal & Splice Type	Tab
Quick Disconnect Terminal Orientation	Straight
Contact Base Material	Phosphor Bronze
Crimp Type	F-Crimp
Barrel Type	Open

Mechanical Attachment

	.055 in
Mating Retention Type	Locking Lance
Wire Insulation Support	With

Dimensions

Accepts Wire Insulation Diameter Range	3.1 – 4.1 mm[.122 – .161 in]
Overall Length	28.1 mm[1.1 in]
Receptacle Terminal Stock Thickness	.41 mm[.016 in]
Wire Size	.82 – 2.08 mm²
Quick Disconnect Mating Tab Width	6.35 mm[.25 in]
Quick Disconnect Mating Tab Thickness	.81 mm[.032 in]

Usage Conditions

Insulation Requirement	Uninsulated
Operating Temperature Range	-40 – 110 °C[-40 – 230 °F]

Industry Standards

UL Flammability Rating	UL 94V-2
------------------------	----------

Packaging Features

Packaging Quantity	500
Quick Disconnect Packaging Method	Loose Piece/Carton

Other

Comment	Without Locking Hole
---------	----------------------

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant



China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JAN 2021 (211) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 154660-2
FASTON 250 TAB 22-18 AWG TPBR



TE Part # 928906-2
FF 110 TAB 20-15 AWG .016 TPPB



TE Part # 641256-1
BLADE TAB 250 18-14AWG BR LP

Also in the Series | FASTIN-FASTON 250




Crimp Terminal Housings(216)



Insertion & Extraction Tools(2)



PCB Terminals(2)




Quick Disconnects(258)

Customers Also Bought



TE Part #163081-8
TYPE III CONTACTS STRIP EMEA



TE Part #163006
6 WAY FASTIN-ON HOUSING REC NATURAL



TE Part #160450-2
FF 250 TAB 18-14AWG TPPB



TE Part #1393725-4
C42334A 41A 6=RP622 FEDERLEI



TE Part #1534188-1
LOW & MEDIUM POWER HEADER



TE Part #1-967627-3
TIMER, CONNECTOR HOUSING



TE Part #HC5884
STANDARD BAT CLMP NEGATIVE



TE Part #1106408-2
HIP-K.3/4.STO.1.M16.G



TE Part #1106408-3
HIP-K.3/4.STO.1.M20.G



TE Part #1106434-4
HD.24.STS.1.M32.G

Documents

Product Drawings

FF 250 TAB 18-14AWG TPPB LP

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_160451-2_D.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_160451-2_D.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_160451-2_D.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages



1654742_HOUSEHOLD_APPLIANCES_RAST5

English

Product Specifications

FASTIN-FASTON CONN. .110 INCH, .187 INCH, .250 INCH, .375 INCH SRS.

English

Product Specification

English